




Nitrile

Extra durability with a thin, moisture absorbing flock lining

- Soft, flock lining absorbs moisture
- Thick design resists punctures and tears
- Durable nitrile for reliable splash protection



Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment

Recommended For

- Production line support and maintenance
- General Purpose Auto Aftermarket
- Assembly and inspection of components



TECHNICAL DATA SHEET

PRODUCT INFORMATION

	Dura Flock® DFK-608
Material	Nitrile
Color	Green
Glove Design	Flock Lined, Fully Textured
Cuff	Beaded
Manufacturing/QMS Audit Standards	ISO 9001:2008
Regulatory/Standards Compliance	EN 420:2003 + A1:2009, EN 421:2010
Packaging	50 gloves per dispenser 10 dispensers per case 500 gloves per case
Storage	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country of Origin	China
User Needs Segment	Robust
Available sizes	S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10), XXL (10.5 - 11)
Anti-static	No

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	270 / 10.6		ASTM D3767, EN 420
Freedom from Holes (Inspection level I)	2.5 AQL		ASTM D5151, EN 455-1
Palm Thickness (mm/mils)	0.21 / 8.3		ASTM D3767, EN 420
Finger Thickness (mm/mils)	0.20 / 7.9		ASTM D3767, EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	≥ 14	≥ 19	ASTM D412 & D573
Elongation at Break (%)	≥ 500	≥ 400	ASTM D412

ORDERING INFORMATION

Size	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)	XXL (10.5 - 11)
Product Code	DFK-608-S	DFK-608-M	DFK-608-L	DFK-608-XL	DFK-608-XXL

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia

Ansell PYC
Ten. +7 495 258 13 16

Performance Standards and Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.