



M-8358

2



SHROUD WILL ACCEPT 3/16" (5mm) PADLOCK FOR OSHA LOCKOUT/TAGOUT COMPLIANCE

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
COVER	NYLON	BLACK
CORD CLAMPS	NYLON	WHITE
INSERT (4&5 WIRE)	NYLON	BLACK
SHROUD	VALOX	WHITE
BLADE HOLDER	NYLON	NATURAL
RETAINER	POLYCARBONATE	CLEAR
BLADE 20A	.080 BRASS	*
BLADE 30A	.070 BRASS	*
WIRE CLAMP	.080 CRS	NICKEL PLATE
#10 TERMINAL SCREWS	BRASS	*
#10 GROUND SCREW	BRASS	GREEN
ASSEMBLY SCREWS	STAINLESS STEEL	
CORD CLAMP SCREWS	STEEL	ZINC PLATE
DUST SHIELD	EPDM	BLACK

* WHITE FINISH ON NEUTRAL BLADE AND TERM SCREW WHEN USED

NEMA NO.	CAT NO.	RATING	POLE/WIRE GROUNDING	VOLTAGE/COLOR CODE	CORD RANGE	DIM "A"	DIM "B"	DIM "C"
L5-20P	HBL2311S	20A 125V	2P/3W	YELLOW	ø.36 TO .93 (9-24)	4.21 (106.9)	ø2.04 (51.8)	ø2.26 (57.4)
L6-20P	HBL2321S	20A 250V	2P/3W	BLUE	ø.36 TO .93 (9-24)	4.21 (106.9)	ø2.04 (51.8)	ø2.26 (57.4)
L7-20P	HBL2331S	20A 277VAC	2P/3W	GRAY	ø.36 TO .93 (9-24)	4.21 (106.9)	ø2.04 (51.8)	ø2.26 (57.4)
L5-30P	HBL2611S	30A 125V	2P/3W	YELLOW	ø.36 TO .93 (9-24)	4.21 (106.9)	ø2.04 (51.8)	ø2.26 (57.4)
L6-30P	HBL2621S	30A 250V	2P/3W	BLUE	ø.36 TO .93 (9-24)	4.21 (106.9)	ø2.04 (51.8)	ø2.26 (57.4)
L14-20P	HBL2411S	20A 125/250V	3P/4W	ORANGE	ø.35 TO 1.15 (9-29)	4.21 (106.9)	ø2.23 (56.6)	ø2.33 (59.2)
L15-20P	HBL2421S	20A 3ø 250VAC	3P/4W	BLUE	ø.35 TO 1.15 (9-29)	4.21 (106.9)	ø2.23 (56.6)	ø2.33 (59.2)
L16-20P	HBL2431S	20A 3ø 480VAC	3P/4W	RED	ø.35 TO 1.15 (9-29)	4.21 (106.9)	ø2.23 (56.6)	ø2.33 (59.2)
L14-30P	HBL2711S	30A 125/250V	3P/4W	ORANGE	ø.35 TO 1.15 (9-29)	4.21 (106.9)	ø2.23 (56.6)	ø2.33 (59.2)
L15-30P	HBL2721S	30A 3ø 250VAC	3P/4W	BLUE	ø.35 TO 1.15 (9-29)	4.21 (106.9)	ø2.23 (56.6)	ø2.33 (59.2)
L16-30P	HBL2731S	30A 3ø 480VAC	3P/4W	RED	ø.35 TO 1.15 (9-29)	4.21 (106.9)	ø2.23 (56.6)	ø2.33 (59.2)
L17-30P	HBL2741S	30A 3ø 600VAC	3P/4W	BLACK	ø.35 TO 1.15 (9-29)	4.21 (106.9)	ø2.23 (56.6)	ø2.33 (59.2)
L21-20P	HBL2511S	20A 3øY120/208VAC	4P/5W	BLUE	ø.35 TO 1.15 (9-29)	4.21 (106.9)	ø2.23 (56.6)	ø2.33 (59.2)
L21-30P	HBL2811S	30A 3øY120/208VAC	4P/5W	BLUE	ø.35 TO 1.15 (9-29)	4.21 (106.9)	ø2.23 (56.6)	ø2.33 (59.2)
L8-20P	HBL2341S	20A 480V	2P/3W	RED	ø.36 TO .93 (9-24)	4.21 (106.9)	ø2.04 (51.8)	ø2.26 (57.4)
L8-30P	HBL2641S	30A 480V	2P/3W	RED	ø.36 TO .93 (9-24)	4.21 (106.9)	ø2.04 (51.8)	ø2.26 (57.4)

NOTE:

- ALL SCREWS ARE COMBINATION DRIVE HEAD, #1 ROBERTSON/SLOT/#2 PHILLIPS.
- DIMENSIONS ARE IN INCHES/mm.

2	ADDED "SEE TABLE" & NOTE 2 PER DCN 8685	TCM	11/26/01
1	RELEASED PER DCN 7839	JEZ	8/1/00
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE SAFTEY SHROUD
TWIST LOCK PLUGS
3,4&5 WIRE, 20&30 AMP

TOLERANCES UNLESS OTHERWISE SPECIFIED
FRACTIONS N/A
DECIMALS N/A
ANGLES N/A

WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
BRIDGEPORT, CT

DR. BY B.C. APP. BY JEZ
TR. BY SCALE NONE
CHK'D BY JEZ DATE 02/12/98

DIMENSION SHEET FOR CAT. NO.

REPAIRABLE

NON-REPAIRABLE

B

M-8358

2