



Item # M-48

Non-Sparking, Non-Magnetic, Corossion Resistant

Kit includes:

- 8" Combination Pliers: P-31
- Shoe Handle Brush: B-399
- Putty Knife (Stiff) 1-1/4" x 3-9/16" Blade, 7-3/4" OAL: K-21
- Common Knife 3-1/8" Blade, 6-3/4" OAL: K-1
- 10" Groove Joint Pliers: P-39
- #2 Phillips Screwdriver: S-1099
- Std. Screwdriver - 5/16" Tip, 6" Blade: S-49
- 16 oz. Claw Hammer with Fiberglass Handle: H-20FG
- 6" Adjustable Wrench: W-70
- 10" Adjustable Wrench: W-72
- 10" Adjustable Pipe Wrench: W-211
- Tool Box: M-49-Box



Specifications

-

length (mm)

405

width (mm)

235

height (mm)

205

Wt (g)	4740
length (in)	16
width (in)	9-1/4
height (in)	8
Wt (lbs)	10.45