









Combination Wallplates, 2-Gang

Description	Color	Thermoplastic		Material	Metal Catalog Number
		Standard	Mid-Size		
2-Gang, 1-Toggle, 1-Duplex 	Brown	P18	–	Aluminum	①
	Gray	P18GY	PJ18GY	Brass	SB18
	Ivory	P18I	PJ18I	Brass Plated	–
	Light Almond	P18LA	PJ18LA	Chrome	SCH18
	Red	P18R	–	S/S 302/304	SS18
	White	P18W	PJ18W		
2-Gang, 1-Duplex, 1-Decorator 	Black	P826BK	PJ826BK	Aluminum	①
	Brown	P826	PJ826	Brass	SB826
	Gray	P826GY	PJ826GY	Brass Plated	①
	Ivory	P826I	PJ826I	Chrome	①
	Light Almond	P826LA	PJ826LA	S/S 302/304	SS826
	Red	P826R	–		
2-Gang, 1-Toggle, 1-Decorator 	Black	P126BK	–	Aluminum	①
	Brown	P126	PJ126	Brass	SB126
	Gray	P126GY	PJ126GY	Brass Plated	–
	Ivory	P126I	PJ126I	Chrome	①
	Light Almond	P126LA	PJ126LA	S/S 302/304	SS126
	Red	P126R	–		
2-Gang, 1-Toggle, 1-Decorator White P126W	White	P126W	PJ126W		
2-Gang, 1-Single Receptacle 1.40 in. (35.6) Hole, 1-Duplex 	Ivory	P78I	–	Aluminum	①
	White	P78W	–	Brass	①
2-Gang, 1-Single Receptacle 1.60 in. (40.6) Hole, 1-Duplex 				Brass Plated	①
				Chrome	①
				S/S 302/304	SS8720
2-Gang, 1-Toggle, 1-Blank Box Mount 	Brown	–	PJ113	Aluminum	①
	Gray	P113GY	–	Brass	①
	Ivory	P113I	PJ113I	Brass Plated	①
	Light Almond	P113LA	–	Chrome	①
	White	P113W	PJ113W	S/S 302/304	SS113
2-Gang, 1-Toggle, 1-Blank Strap Mount 				Aluminum	①
				Brass	①
				Brass Plated	①
				Chrome	①
				S/S 302/304	SS114
2-Gang, 1-Blank, 1-Decorator Box Mount 	Black	P1326BK	–	Aluminum	①
	Gray	P1326GY	–	Brass	①
	Ivory	P1326I	PJ1326I	Brass Plated	①
	Light Almond	P1326LA	PJ1326LA	Chrome	①
	White	P1326W	PJ1326W	S/S 302/304	SS1426*

Note: Thermoplastic wallplates feature pre-inserted captive screws for faster assembly in single gang configurations.

① Available as a custom wallplate, see pages O-32 to O-34. Consult custom wallplates section for additional openings and combinations.

*Strap Mount.

Dimensions in Inches (mm)