




M-6186

3



CORD CLAMP TAKES CORDS FROM Ø.460 [11.68] TO Ø.720 [18.29]



| CAT. NO.   | HOUSING COLOR | CONFIGURATION | RATING        |
|------------|---------------|---------------|---------------|
| HBL2311VBK | BLACK         | NEMA L5-20P   | 20A 125V      |
| HBL2311VY  | YELLOW        |               |               |
| HBL23CM11V | YELLOW        | NEMA L5-20P   | 20A 125V      |
| HBL2321VBK | BLACK         | NEMA L6-20P   | 20A 250V      |
| HBL2321VY  | YELLOW        |               |               |
| HBL2331VBK | BLACK         | NEMA L7-20P   | 20A 277V.A.C. |
| HBL2331VY  | YELLOW        |               |               |

NOTES: (UNLESS OTHERWISE SPECIFIED)

1) DIMENSIONS ARE: INCHES [MM]

LIST OF PARTS

| DESCRIPTION       | MATERIAL   | FINISH |
|-------------------|------------|--------|
| HOUSING           | NYLON      |        |
| NARROW BLADE      | BRASS      |        |
| WIDE BLADE        | BRASS      |        |
| GROUND BLADE      | BRASS      |        |
| WIRE CLAMP NUT    | C.R. STEEL | NICKEL |
| BINDING SCREW     | STEEL      | COPPER |
| WHITE BIND. SCREW | STEEL      | NICKEL |
| GREEN BIND. SCREW | STEEL      | GREEN  |
| CORD CLAMP SCREW  | STEEL      | ZINC   |
|                   |            |        |
|                   |            |        |
|                   |            |        |
|                   |            |        |

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE  NON-REPAIRABLE

B

M-6186

3

| 3   | REDRAWN ON CAD ON UPDATED FORMAT. ADDED CAT. NO. HBL23CM11V TO TABLE, NOTE 1, AND DUAL DIM.'S. "SEE TABLE" WAS LIST OF CAT. NO.'S. SUPERSEDES DRAWING DATED 3-10-80 PER DCN # 13355. JMN | DJP | 11/20/06 |
|-----|--|-----|----------|
| SYM | REVISIONS  | APP | DATE     |

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE 20A 2-POLE 3 WIRE GROUNDING TWIST-LOCK VALISE PLUG

|                                       |        |   |                   |
|---------------------------------------|--------|---|-------------------|
| TOLERANCES UNLESS OTHERWISE SPECIFIED |        | WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT |                   |
| FRACTIONS                             | ± 1/64 | DR. BY  | P.M. APP. BY DJP  |
| DECIMALS                              | ± .005 | TR. BY  | JMN SCALE FULL    |
| ANGLES                                | ± 2    | CHK'D BY  | DJP DATE 11/16/06 |