

## **Ultra- Spill Decks P6**

## **Product Data Sheet**

Item Number: 1175

Item Name: Ultra- Spill Deck P6

Load Capacity UDL: 9000 lbs. (4082 kg)

Sump Capacity: 66 Gallons (250L)

Item #	Color	Misc. Features	Amount	Length	Width	Height	Weight	QTY/ Pallet
1175	Yellow/Black		1 Each	74 ¼"	50" (1270mm)	5 ¼" (133mm)	86 lbs. (39 kg)	10
				(1886mm)				

**Description:** A polyethylene sump with deck surface large enough to store six 55- Gallon drums. In the event of a leak, fluid is contained in the sump preventing contamination to surrounding environment.

**Application:** For storage of both steel and polyethylene drums and smaller containers which need to meet containment regulations and/or for general housekeeping purposes.

**Product Features:** The Ultra-Spill Decks P6 helps you comply with containment regulations while storing steel and poly drums. Capture leaks, drips, and spills to keep floors dry and workers safe.

- Molded-in sump catches leaks, drips and spills to help you comply with regulations and keep your storage area clean and safe.
- Low profile design reduces safety and handling concerns found with taller spill containment pallets.
- Linear Low-density Polyethylene construction resists UV rays, rust, corrosion and most chemicals for long trouble-free life of the product.
- Removable grates makes clean-up quick and easy.
- Meets SPCC, EPA Container Storage Regulation 40 CFR 264.175 and UFC Spill Containment Regulations.

Composition: 100% polyethylene with UV inhibitors and fluorination gas treatment.

Helps you comply with: 40 CFR 112.7 and 40 CFR 264.175

Additional Specifications: Grate dimensions 3- 48"x24"

**Disclaimers:** <u>Flammables Notice:</u> If using this product with flammable liquids, please consider the regulations that apply to storage and handling of flammable liquids and the safety of this application, specifically flammable vapors, static discharge and heat sources.