Product Data Sheet

Item Number: 1157 / 1158

Item Name: Ultra-IBC SpillPallet Plus

Load Capacity UDL

•8500 lbs./each (3855.6 kg/each)

Sump Capacity

•365 gal./each (1362.6 L/each)

Options Available											
Item #	Size	Color	Misc. Features	Amount	Length	Width	Height	Depth	Int. Dia.	Ext. Dia.	Weight
1157	_	Yellow	Without Drain	1 each	_	62" (157.5cm)	28" (71cm)	62" (157.5cm)	_	_	320lbs. (145.2kg)
1158	_	Yellow	With Drain	1 each	_	62" (157.5cm)	28" (71cm)	62" (157.5cm)	_	_	320lbs. (145.2kg)

Per Pallet: 3

Description

A containment sump with deck surface used for storing and containing any leaks, spills or drips from Intermediate Bulk Containers (IBC's).

Application

Contain leaks, spills or drips from IBC containers.

Product Features

- 28" high lower profile for easier access and dispensing
- All-poly construction chemical-resistant, won't rust or corrode
- Full, flat grate deck surface (52" x 52") easy to position IBCs; no open voids in surface
- Compact 62" x 62" footprint
- 8500 lb. UDL weight capacity
- 2-way forklift entry for easy movement when not loaded
- Available with optional drain

Composition

• Polyethylene

This product helps you comply with:					
Regulatory Citation	Summary				
40 CFR 264.175	Hazardous waste containment systems must be free of structural cracks or gaps, be designed to keep spilled liquids from remaining in contact with the container, prevent run-on and "have sufficient capacity to contain 10% of the volume of the containers, or the volume of the largest container, whichever is greater."				

Disclaimers

• **Notice:** For a chemical compatibility guide call Technical Services at 1-800-353-1611 or visit SpillContainment.com.

