

ORION™ Winter Overshoes



Superior protection against winter's harsh elements.

Navigate the Winter Landscape with Confidence in Orion™ Overshoes

Orion™ combines a sturdy nylon upper with a lightweight polyurethane midsole and a durable TPR outsole to create an anti-fatigue overshoe with heavy-duty performance.

- 840 denier nylon with polyurethane coating is waterproof and durable.
- Roomy interior design to accommodate oversized work boots.
- Extra wide gusset for easy donning and doffing.
- Hook & loop closure allows customizable fit.
- Adjustable instep strap with quick-release buckle for ease of use while wearing gloves.
- Deep lug, cleated outsole provides sure-footed traction in wintry conditions.
- Polypropylene foam liner provides cushioning and insulation.
- 14" standard height with a 6" roll-a-way gaiter expands coverage to 20".
- Reflective accents on all sides offer enhanced visibility in low light conditions.
- Lightweight, anti-fatigue design for all day comfort.



Orion™ Outsole:

The Orion outsole is designed for stability and grip. The thermoplastic rubber (TPR) stays flexible in cold temperatures, and perimeter cleats provide sure-footed stability. Deep lug, self-cleaning treads have a variety of angles and surfaces for traction in snow and slush.

Ideal Applications: Parcel Delivery, Utilities, Construction, Commuting, Public Works, and Winter Work Outdoors.

GRAINGER #	TINGLEY #	SIZE
TPR OVERBOOT – BLACK – CLEATED TPR OUTSOLE		
52NT39	7500G.SM	SM
52NT40	7500G.MD	MD
52NT41	7500G.LG	LG
52NT42	7500G.XL	XL
52NT43	7500G.2X	2X

Size	Fits Men's Work Boots	Fits Women's Work Boots
Small	4 - 5½	6 - 7½
Medium	6 - 7½	8 - 9½
Large	8 - 9½	10 - 11½
X Large	10 - 12	12 - 14
2X Large	13 - 15	

