

# The tether attachment point for the range with multi-component handles

Tools can fall down anytime you are using them from a high height, for example; when using them on cherry pickers, scaffolding, ladders and by industrial climbers working with wire rope hoists.

# KNIPEX offers a wide range of pliers and accessories that can reliably prevent the KNIPEX pliers from falling down.

There is a very stable tether attachment on the inside of the handles which is welded onto the handle for attaching the tether or adapter strap. The lug enables the equipment to be attached and put down quickly. The sophisticated elements from our KNIPEX Tethered Tools Program offers several individual variations for connection and use.

#### Please read all warnings on product packaging carefully

- > Do not use on live circuits. Always switch off power.
- > Always wear approved eye protection.
- > NO PPE = No Personal Protective Equipment.
- > Only for latching tools from the KNIPEX Tethered Tools range, connected and combined in accordance with this description.
- > Tether extends to length of around 5 feet (1.5 m) rig to avoid contact with objects below.
- > Do not use around moving or rotating equipment.
- > Will not support human weight.
- > Inspect for wear before each use. Do not use if evidence of wear.



### The Tool Drop Protection System

for tools with tether attachment

- Versatile application potential ranging from building construction to industrial climbers
- ▶ Reliably prevents the tool from falling down, and can protect against serious injuries, damage to property or loss

### Tether 00

- > wide working radius: flexible tether for user-friendly work
- > variable fastening options: with strap made of a flat belt sewn to one end and a cord and cord stopper sewn into the other end
- > suitable for all KNIPEX pliers with tether attachment



### **Adapter Straps**

**00** 50

- > diverse options for fastening in combination with the carabiner and the tether
- > permits fast, safeguarded switching from the fastener on the tool bag to the tether and from one tool to another
- > suitable for all KNIPEX pliers with tether attachment



#### **Carabiners**

**00** 50


- > with screw lock to prevent accidental opening
- > strong and light aluminum design weighing just 1 ounce
- > for connecting adapter strap and tether or to attach these to a fixed point







00 50 04 T BKA: The complete tethering system set



## Pliers with tether attachment point

**Complete range** 



Pliers range with tether attachment point for a tool tether				
	Product Number	Description		
	02 02 225 T BKA black atramentized; head polished	High Leverage Combination Pliers,		
	08 22 145 T BKA black atramentized; head polished	Needle-Nose Combination Pliers, slim head for use in inaccessible work areas		
	09 02 240 T BKA black atramentized; head polished	Lineman's Pliers, ultra-high leverage design for 25% easier cutting power		
at lo	09 12 240 T BKA black atramentized; head polished	09 12 240 T BKA: with a universal terminal crimper and a fish tape puller on the backside		
	13 02 614 T BKA black atramentized; head polished	Electrician's Pliers, ideal for cable work, gripping and bending wire or even cutting medium hard and hard wire		
	13 82 8 T BKA black atramentized; head polished	Electrical Installation Pliers, multifunctional 6-in-1 pliers for electrical installation; cutting, stripping, crimping, gripping, bending and deburring		
	26 12 200 T BKA black atramentized; head polished	Long Nose Pliers w/Cutter, elastic precision tips will not deform or bend and will spring back into place		
	26 22 200 T BKA black atramentized; head polished	26 22 200 T BKA: with 40° angled tips for hard to reach spaces		
	71 02 200 T BKA black atramentized	KNIPEX CoBolt® Compact Bolt Cutters, particularly high cutting performance with little physical effort		
	71 22 200 T BKA black atramentized	71 22 200 T BKA: 20° angled head with single-sided joint bar and diagonal cutting edge for almost flush cutting		
	71 32 200 T BKA black atramentized	71 32 200 T BKA: notch in the blade for cutting thicker wire		
	74 02 200 T BKA black atramentized; head polished	High Leverage Diagonal Cutters, high cutting performance with minimum effort. Available in 8" and 10" lengths		
	74 02 250 T BKA black atramentized; head polished			
	74 22 200 T BKA black atramentized; head polished	12° angled head in a 8" length		
	74 22 250 T BKA black atramentized; head polished	12° angled head in a 10" length		

Product Number	Description
86 05 180 T BKA chrome plated	Pliers Wrenches, pliers and a wrench in a single tool, for damage free installation of plated fittings; Available in 7 1/4" and 10" lengths
86 05 250 T BKA chrome plated	
87 02 180 T BKA grey atramentized; head polished	KNIPEX Cobra® High-tech Water Pump Pliers, grips any shaped object — round, square, hex or flat. Push-button adjustment means that once th capacity is set, it stays set. Available in 7 1/4", 10" and 12" lengths
87 02 250 T BKA grey atramentized; head polished	
87 02 300 T BKA grey atramentized; head polished	
88 02 250 T BKA black atramentized; head polished	KNIPEX Alligator® Water Pump Pliers, self-locking on pipes and nuts – no slipping off the workpiece, box-joint design for high stability Available in 10" and 12" lengths
88 02 300 T BKA black atramentized; head polished	
95 12 165 T BKA burnished	Cable Shears, precision ground, hardened blades: clean and smooth cut without crushing and deformation
95 62 190 T BKA head polished	Wire Rope Cutter, special blade geometry prevents the wire rope from fanning out

	Product Number	Description
	26 16 200 T chrome plated	Snipe Nose Side Cutting Pliers, (Stork Beak Pliers), extremely durable, elastic precision tips; half-round, long, pointed jaws
	26 26 200 T chrome plated	26 16 200 T: straight 26 26 200 T: bent
-/ij	70 06 160 T chrome plated	Diagonal Cutter, slim head for use in inaccessible work areas; available with fall protection in a compact length of 160 mm and a robust 180 mm length
at a bank	70 06 180 T chrome plated	N
2. All Margines	74 06 200 T chrome plated	High Leverage Diagonal Cutters, high cutting performance with minimum effort; Available with fall protection in lengths of 200 mm and 250 mm
	74 06 250 T chrome plated	N
C <sup>2</sup>	87 26 250 T chrome plated	KNIPEX Cobra® VDE, High-Tech Water Pump Pliers, push the button for adjustment on the workpiece and nuts
<b>O F</b>	95 16 165 T chrome plated	Cable Shears, precision ground, hardened blades: clean and smooth cut without crushing and deformation

	Product Number	Description
	00 50 01 T BK	1 x Tether Wide working radius: the tether made of gathered fabric tape expands to a length of approx. 1.5 m when under strain
	00 50 02 T BK	3 x Adapter straps Flexible connection between tool and the reliable tether point
00	00 50 03 T BK	2 x Carabiner When tightened, the screw lock prevents inadvertent opening of the carabiner
	00 50 04 T BK	Tethering System Set For diverse options for attaching KNIPE) pliers using the tether attachment (1 x Tether, 3 x Adapter straps, 2 x Carabiner)