

ProTac® HL-X USB / ProTac® HL-X

MULTI FUEL - 18650 USB LI-ION RECHARGEABLE or 2x CR123 FLASHLIGHT

MARKET

APPLICATIONS: Professional Light - Hardware/Tool, Industrial, Law Enforcement, Security, Automotive, Sporting Goods, Consumer.

DESCRIPTION:

The ProTac® HL-X USB or ProTac® HL-X are 1000 lumen tactical flashlights that can use either a proprietary Streamlight 18650 USB rechargeable Li Ion Battery or two CR123A disposable batteries. The ProTac® HL-X USB is a complete rechargeable system that comes with a charge cord and an 18650 button top battery that features an integrated mirco-USB charge port. The ProTac® HL-X comes packaged with two CR123A batteries. Both versions feature a tactical tail cap switch for momentary or constant on operation, three different user selectable programs and a pocket clip for convenience. The aluminum housing with Type II Military Spec anodizing helps make the light extremely durable and abrasion resistant. Packaged with a removable pocket clip and holster.

CASE MATERIAL:

6000 series machined aircraft aluminum with Type II MIL-Spec anodized finish. Available in black.

DIMENSIONS:

Length: 5.43 in. (13.8 cm) Head Diameter: 1.44 in. (3.7 cm) Body Diameter: 1.0 in. (2.54 cm)

WEIGHT:

ProTac® HL-X USB: 6.2 oz (176 grams) with one Streamlight 18650 USB Li-Ion battery (included in purchase).

ProTac® HL-X: 5.7 oz (162 grams) with two CR123A batteries (included in purchase).

LENS:

Glass with anti-reflective coating; gasket sealed.

LIGHT SOURCE:

C4® LED technology, impervious to shock with a 50,000 hour lifetime.

LIGHT OUTPUT:

See chart. Fully regulated output for consistent lumen performance over the battery life.

ON/OFF:

Multi-function, push-button tactical tail switch. One handed operation of momentary, variable intensity or strobe mode. TEN-TAP® programmable switch allows user selection of one of three different programs: high/strobe/low (factory default), high only, or low/medium/high.

RUN TIME:

See charts for specific battery type. All runtime claims are to 10% of initial lumen output.

BATTERY:

One (1) Streamlight 18650 USB Li-Ion protected 3.7V, 2600 mAh rechargeable battery, recharges in 5 hours.

Two (2) 3 Volt CR123A lithium batteries with a storage life of 10 years.

FEATURES:


C4® LED technology for extreme brightness.

IP68 rated; dust tight and waterproof to 2 meters. All openings o-ring sealed.

2 meter impact resistance tested.

Multi fuel; accepts 18650 Li-Ion or CR123A batteries.

TEN-TAP® programmable switch allows user to select one of three different programs.

Anti-roll face cap.

Serialized for positive identification.

Removable pocket clip and Holster.

APPROVALS:

☑ Meets applicable European Community Directives.

Ⓢ CEC Compliant (ProTac® HL-X USB only)

WARRANTY:

Streamlight's Limited Lifetime Warranty

OPTIONAL
ACCESSORIES:

Holster, Charge cords.

	WITH CR123A BATTERIES				WITH 18650 RECHARGEABLE BATTERY			
	FL1 STANDARD	HIGH	MEDIUM	LOW	FL1 STANDARD	HIGH	MEDIUM	LOW
OUTPUT		1000 LUMENS	400 LUMENS	65 LUMENS		1000 LUMENS	400 LUMENS	65 LUMENS
RUNTIME		1h 15min	3h	20h		1h 30min	3h 30m	23h
DISTANCE		330m	200m	80m		330m	200m	80m
INTENSITY		27,100cd	10,000cd	1,600cd		27,100cd	10,000cd	1,600cd
	Strobe Run Time: 2 Hr 30 Min				Strobe Run Time: 3 Hr 15 Min			

