

PRODUCT FACT SHEET

VANTAGE® 180 X

HELMET MOUNTED/RIGHT ANGLE/HAND HELD MULTI-FUNCTION MULTI-FUEL LIGHT

Fire & Rescue, Law Enforcement, Industrial Security, Public Works & Utilities MARKET:

DESCRIPTION: Lightweight and compact, the VANTAGE® 180 X is designed to easily attach above or below full brim Fire and

> Industrial helmets. The VANTAGE® 180 X features a C4®LED main light combined with an ultra-bright blue LED safety tail light or a white safety flood down light mode automatically selected with the rotation of the head. Integrated Stainless Steel Clip is designed to be used with the "quick release" helmet bracket that easily detaches the light from the helmet for use as a hand held or pocket light. The light also features a clip to attach to turnout gear. The VANTAGE® 180 X is powered by a Streamlight 18650 USB rechargeable Li-Ion battery or two CR123A disposable batteries. The VANTAGE® 180 X features the latest in C4® LED technology. Sealed for

water-resistance.

CASE MATERIAL: High-impact "Super Tough" nylon chemically-resistant engineering polymer for exceptional durability and sure

grip. Available colors: "safety orange" with black tail cap and trim or light is also available in all black.

DIMENSIONS: Height: 5.20 in. (13.20 cm) Head Diameter: 1.60 in. (4.06 cm) Body Size: 1.06 in. (2.69 cm)

5.5 oz. (156 grams) with two CR123 Lithium batteries. WEIGHT:

5.9 oz. (167 grams) with one 18650 USB rechargeable battery.

LENS: Unbreakable polycarbonate with a silicone anti-scratch coating. O-ring sealed.

Main light: C4®LED technology, impervious to shock with a 50,000 hour lifetime. Rear light: Ultra-bright blue **LIGHT SOURCE:**

safety tail light or white safety flood down light.

LIGHT OUTPUT: 7200 candela peak beam intensity, 170m beam distance and 250 lumens measured system output.

Optimized electronics provide regulated intensity. Custom "Total Internal Reflection" optic for narrow beam with optimum peripheral illumination to aid in navigation. Ultra-bright blue rear light for helmet mount use in heavy smoke or a white safety flood down light mode when head is rotated 90 degrees towards push button.

See charts for specific battery type. All claims to 10% of initial lumen output. **RUN TIME:**

Body mounted push button switch provides one handed constant "on" operation. Fast double click to low mode. ON/OFF/MODE:

Rotate head 90 degrees towards push button automatically changes rear LED from blue safety light to white

safety down light.

One (1) Streamlight 18650 USB Li-Ion protected 3.7V, 2600mAh rechargeable battery, recharges in 5 hours. **BATTERIES:**

Two (2) 3 Volt CR123A lithium batteries with a storage life of 10 years.

FEATURES: C4®LED technology for extreme brightness.

180 degree rotating head automatically changes blue tail light to white down light. Helmet bracket, included with purchase, features quick release to detach light.

Turnout gear attachment hook. 1 meter impact resistance tested.

IPX7 rated design; waterproof to 1 meter for 30 minutes.

Integrated Stainless steel multi-function clip for a variety of attachment methods and mounting positions.

Ultra-bright blue LED safety tail light visible in heavy smoke.

LED Solid State Power Regulation provides maximum light output throughout battery life.

Individually serialized for positive identification.

APPROVALS: Meets requirements of NFPA 1971-8.6 (2013).

CE

Meets applicable European Community Directives.

CEC Compliant (18650 USB only). (BC)


WARRANTY: Streamlight's Limited Lifetime Warranty

ACCESSORIES:

CR123A BATTERIES

250 100 **OUTPUT** LUMENS LUMENS **RUN TIME** 4h 12h DISTANCE 170m 103m INTENSITY 7,200cd 2,650cd

18650 USB LI-ION BATTERY		
FL1 STANDARD	HIGH	LOW
314	250 LUMENS	100 LUMENS
(1)	5h	15h
	170m	103m
	7,200cd	2,650cd



All performance claims tested to ANSI/NEMA FL1-2009 Standard

Issued: 12/16/2016