

TradeSelect
Straight Blade Devices
15A, 125V, 2 Pole, 3 Wire Grounding
Tamper Resistant Decorator Duplex

HUBBELL



Ordering Information

Device Color	UPC	Catalog Number
White	883778301681	RRD15SWTR

Listings

NEMA WD1 and WD5, UL 498

Specifications

Grade	Residential
Size	Standard Sized
Connection Type	Push and Side Wire
Mounting Type	Screw, Flush
Wattage	1,875 Watt
Wire Size	#14 AWG to #12 AWG
Material	Thermoplastic
NEMA Rating	5-15R

Performance

Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

Environmental

Flammability	UL 94 V-2
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

