# HDCM3 8" LED Monitor with 1280 x 720 resolution

## Connects using HDMI, VGA, and AV inputs

#### Features:

- Use with Security Cameras during setup, testing, and monitoring; DVRs, Cable/Satellite TV boxes, and DVD Players; Computers and Laptops as a second monitor; DSLR Cameras as a second screen while broadcasting live events; Raspberry PI Projects, and much more
- Versatile stand allows placement on top of desk or DVR/NVR, mounting to wall, or mounting to IT cabinet or server rack
- Full HD 1080p screen resolution
- · Built-in speaker
- Volume control button
- Ruggedized outer construction
- · Mounts to a desk or wall using the included swivel stand
- Includes wall-or desk-mountable swivel stand, AC adapter/ charger and 1500mAh Lithium rechargeable battery
- 1-year warranty



### **Specifications**

-	
	8" TFT LED
Backlight Lamp	LED Backlight
Resolution	1280 x 720
Aspect Ratio	16:9
Brightness	450cd/m2
Response Time	>5ms
Contrast	1000:1
Viewing Angle	178°/178°
Display Mode	HDMI (1080p, 1080i, 720p)
Audio	1 BNC input; 3.5mm earphone jack;
	Built in 1W speaker in front panel
Languages	Nine: English, French, Spanish, Italian, German, Russian,
	Korean, Japanese, Chinese
Power	100 to 240VAC, rechargeable battery, or 12VDC/2A
Dimensions	7.4 x 5.2 x 1.2" (188 x130.7 x 31mm)
Weight	1lb (0.45kg)

#### **Ordering Information:**

HDCM3

8" HD TFT LED Monitor





CE



850 Perimeter Road • Manchester, NH • (603) 669-6400 • info@triplett.com