

9080GF6B

Terminal block, Linergy, end barrier, natural color, for 9080GF6, 9080GS6, or 9080GG6 terminal blocks



Main

Range of Product	9080G
Product or Component Type	End Barrier

Complementary

Material	Nylon
Color	Natural
Package Quantity	Set of 10
Mounting Type	35 mm DIN rail 9080GH track
Height	1.5 in (38.10 mm)
Width	2.19 in (55.63 mm)
Depth	0.12 in (3.05 mm)

Environment

Ambient air temperature for operation	-40...257 °F (-40...125 °C)
---------------------------------------	-----------------------------

Ordering and shipping details

Category	21702 - 9080 G (NOT GCB)
Discount Schedule	CP5
GTIN	785901155041
Nbr. of units in pkg.	1
Package weight(Lbs)	0.16 oz (4.5 g)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.61 in (4.1 cm)
Package 1 width	0.20 in (0.5 cm)
Package 1 Length	2.20 in (5.6 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	10

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------