



High-Leverage Ironworker's Pliers



These Klein Tools High-Leverage Ironworker's Pliers have induction hardened side-cutting knives for improved durability and a longer lifespan. They have heavy duty knurled jaws and a spring-loaded self-opening on hot-riveted joint for smooth, easy, and powerful action. The high-leverage design with "handform" handles and the rivet being closer to the cutting edge allows for 46 percent more cutting and gripping power.

Specifications

Type:	Ironworker's Pliers	Application:	Soft Annealed Rebar Tie Wire
Special Features:	Spring Loaded	Overall Length:	9.35" (23.7 cm)
Material:	Steel	Nose Type:	Square
Jaw Length:	1.594" (4 cm)	Jaw Width:	1.24" (3.1 cm)
Jaw Thickness:	0.625" (1.6 cm)	Jaw Capacity:	1.375" (3.5 cm)
Knife Length:	0.781" (2 cm)	Joint Type:	Hot Riveted
Handle Color:	Blue	Handle Finish:	Plastic-Dipped
Handle Length:	7.375" (18.7 cm)	Insulated:	No
Tether Capable:	No	Weight:	1.1 lb (0.5 kg)