

## **Midget Plugs and Flanged Inlets**



HBL7465V




HBL7594V



HBL7594



HBL7570



HBL7466, HBL7467



Dimensions in Inches (mm)







Plugs		15A 125V NEMA ML-1P	15A 125V NEMA ML-2P	15A 125/250V AC NEMA ML-3P
Description	Cord Dia.	Catalog Number		
Valise® plug, black nylon, multiple drive screw terminals.	.220"385" (5.6-9.8)	HBL7465V*	-	-
Valise® plug, black nylon, insulation displacement terminals.	.300"430" (7.6-10.9)	-	HBL7594V	-
Black nylon cover, phenolic body, multiple drive screw terminals.	.281"421" (7.1-10.7)	-	HBL7594	-
Angle plug, black nylon cover, phenolic body, multiple drive screw terminals.	.335"421" (8.5-10.7)	-	HBL7570	-
Valise® plug, black nylon, with insulation displacement terminals.	.300"430" (7.6-10.9)	-	-	HBL7485V*
Black nylon body, phenolic base, multiple drive screw terminals, cord grip.	.281"421" (7.1-10.7)	-	-	HBL7485*
Same as above, except angle cord grip.	.335"421" (8.5-10.7)	-	-	HBL7432*

## Flanged Inlets

Description	Catalog Number		
Stainless steel flange, polarized, exposed terminals.	HBL7467*	-	-
Stainless steel flange, not polarized, exposed terminals.	HBL7466*	-	-
Exposed terminals, black nylon flange.	-	HBL7595N	-
Exposed terminals, stainless steel flange.	-	HBL7595	-
Covered terminals, stainless steel flange, accepts cord .500" (12.7) dia.	-	HBL7551	-
Exposed terminals, black nylon flange.	-	-	HBL7486N*
Exposed terminals, stainless steel flange.	-	_	HBL7486*

Note: See page B-10 for accessories.
\*UL Listed only.
Male ML-2P devices have hollow center ground sleeves.
Male ML-3P devices have solid center neutral pins.



2X .15" (3.8) DIA. HBL7486N

