

# K Body® REVO™



Simply better.

BESSEY® Parallel Bar Clamp, 1500 lbs. (nominal) of clamping force

The K Body® REVO™ Parallel Clamp is a powerful tool designed where 90 degree, high pressure clamping or powerful spreading is required.

- 1 These are arguably the most powerful and most parallel clamps in the world. The three large removable (if you want to clean or replace them) pressure caps are resistant to glue, paint and solvents.
- 2 High quality 2K composite handle with soft plastic insert for comfort while working.
- 3 The rail protection pieces (made from impact resistant polyamide) prevent glue dripping on to the rail. With TK-6 table clamps you can easily fasten the rail protection pieces to a work surface.
- 4 End-clip ensures clamp sits parallel to work surface and is removable to reverse sliding arm for use as spreader.

## Accessorize

Several accessories are available for the K Body® REVO™ or purchase your REVO™ as a kit with your favorite accessory.



### KP Blocks

Rail and stile jig for set up of raised panel doors, frames, boxes, etc.



### K Body® Extender

Connect any two BESSEY® K Body® clamps for extended reach.



### KR-AS Adapter

Attach KR-AS adapter pivoting jaws to any K Body® REVO™ to clamp or spread irregular angles from -15° to +15°.



### TK-6

Use with rail protection pieces to hold to workbench.



Catalog Number	Nominal Throat	Nominal Opening	Clamping Force	Pack Size	GTIN Code (2 pk.)	UPC Code
KR3.512	3 3/4"	12"	1500 lbs	2	10091162006242	091162006245
KR3.518 <b>NEW</b>	3 3/4"	18"	1500 lbs	2	10091162006358	091162006351
KR3.524	3 3/4"	24"	1500 lbs	2	10091162006259	091162006252
KR3.531	3 3/4"	31"	1500 lbs	2	10091162006266	091162006269
KR3.540	3 3/4"	40"	1500 lbs	2	10091162006273	091162006276
KR3.550	3 3/4"	50"	1500 lbs	2	10091162006280	091162006283
KR3.560	3 3/4"	60"	1500 lbs	2	10091162006297	091162006290
KR3.582	3 3/4"	82"	1500 lbs	2	10091162006303	091162006306
KR3.598	3 3/4"	98"	1500 lbs	2	10091162006310	091162006313



Rev. June 12-2012



www.besseytools.com

BESSEY® Tools North America  
1-800-828-1004 · Fax (519) 621-3442