Straight Blade Devices 30A, 125/250V, 3 Pole, 3 Wire Non-Grounding Plug

HUBBELL

Features

- Supertough nylon housing
- Gripping ribs provide secure gripping area
- Captive Allen head terminal screws are user-ready

Ordering Information

Description Cord Diameter UPC Catalog Number .625"-1.00" Plug, Insulgrip®, nylon 783585015699 HBL9337C (15.9-25.4)



Listings

UL Listed File E1706 **CSA Certified**

Specifications

Housing Supertough Nylon

Blade Holder Reinforced Thermoplastic Polyester

Blades **Brass Box Terminals** Copper Alloy

Cord Clamps Reinforced Thermoplastic Polyester



Ø.625 TO Ø1.310 [15.88] [33.27]

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current Dielectric Voltage

Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device Terminal Accommodation #12 AWG through #4 AWG copper wire only

Terminals identified in accordance with UL 498 and CSA **Terminal Identification**

Environmental

Flammability UL 94 HB IP Suitability

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)

Resources

Customer Use Drawing eCatalog

