



R-167

High visibility impact protection with a padded palm and enhanced cut protection.



Impact



Abrasion Protection



Cut



Vibration



Light Duty

Impact and cut protection with synthetic red leather padded palm and touchscreen compatibility for comfort and ease-of-use.

The Ringers 167 Level 1 rated impact glove combines protection against impact hazards with added cut protection of A3, with enhanced durability and comfort due to a synthetic leather padded palm.

- Developed with Ringers' F3 Technology™ and patented TPR design for superior dexterity and comfort.

- Touchscreen compatible index, middle and thumb tips lessen the need to remove gloves.

- High visibility and hook and loop pull tab closure provides added security on the job.



Industries

- Manufacturing
- Mining
- Oil and gas
- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Utilities
- Warehousing

Applications

- General Purpose Auto Aftermarket
- Handling structural and body components
- Body painting including surface inspection
- Applying sealers, touching up
- Body panel repair and replacement
- Oil, fluids and filter change
- Engine transmission and repair
- Tire rotation & changes
- Seizing structural and body parts
- Equipment repair & maintenance
- Assembly and disassembly of equipment
- Final assembly
- Final inspection
- Signalling/Positioning
- Operating of heavy machinery
- Hydraulic set and testing
- Loading and hauling
- Equipment maintenance Scaffolding Pipe handling and insulation Plumbing and sand blasting
- Makeup and breakout tools
- Unloading and stacking pipe
- Set-up of pressure manifold and tubing injector head
- Handling of tools



R-167

High visibility impact protection with a padded palm and enhanced cut protection.

Key Features

- TPR impact protection on top of hand and fingers, certified ANSI/ISEA 138 Level 1
- Flexible knuckle TPR design with two detached fingers
- Durable synthetic leather palm for enhanced grip
- Padded palm for comfort
- Touchscreen compatible index, middle and thumb tips
- Secure cuff closure with hook and loop rubber pull tab
- Reinforced thumb, index, and middle finger tips
- Wrap around index finger protecting wear and tear zone
- High visibility for increased safety

Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	COLOR	PACKAGE
RINGERS R167	Liner Material: N/A Cuff Style: Adjustable		8, 9, 10, 11, 12, 13	Yellow Hi Viz	• 5 pairs/bag, 10 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

