

CHROME SLT®

Elastic loop for secure attachment to tool belt



Elastic cuff with Velcro® closure for a secure fit

Back-of-hand impact guards provide ANSI/ISEA 138 Level 2 protection on knuckles and fingers

Form-fitting, quality materials

High dexterity

Goatskin leather construction with Kevlar® stitching provides a traditional style of comfort

OilGuard® treated leather helps delay saturation issues

Aramid and steel blend liner for 360° cut protection (interior layer)

Grip in dry or light oil situations



4069 Chrome SLT®

PROTECTION ZONES:

		ANSI/ISEA CUT	GRAM SCORE
		A9	7566
		ANSI/ISEA PUNCTURE	ANSI/ISEA 138
		4	
		EN388: 2016	EN407: 2020
		3X43FP	X1XXXX

• Lab tested in accordance with HRC ATPV: 8.6 Cal/cm2 for a level 2 performance

ATTRIBUTES:

Style:	Mechanics
Grip:	Dry or light oil
Cuff Style:	Elastic with Velcro®
Sizes:	6/XS through 12/3XL

FEATURES:

HexArmor® Chrome SLT® gloves are built for a wide array of applications. Each product in the series was crafted to fit the hand with a specific purpose. With multiple styles and various safety features, you can be confident that the Chrome SLT® will keep your hands protected against almost any hazard. Our Chrome SLT® gloves were designed with ultimate comfort in mind, providing unsurpassed dexterity while maintaining cut and puncture resistance. With options for cold weather protection, your hands can stay safe and comfortable in any environment.

HexArmor®

Call **1-877-MY ARMOR** or visit **hexarmor.com**

HexArmor® products are cut and puncture resistant, NOT CUT AND PUNCTURE PROOF. Do not use with moving or serrated blades or tools. User shall be exclusively responsible to assess the suitability of the product as specified for any individual application or use. Protection zones are to be used as a general guide. Actual product protection zones may differ. Product features, design, protection zones subject to change.

Protected by patents and patents pending