

Series 7400 Kraftform pistol grip, adjustable torque screwdrivers (25.0-55.0 in. lbs.)
with Rapidaptor quick-release chuck, art. no. 7447 x 25-55 in. lbs.
Series 7400 Kraftform Torque Screwdrivers



EAN:	4013288102904	Size:	218x81x51 mm
Part number:	05074712001	Weight:	277 g
Article number:	7400 Pistole inch	Country of origin:	CZ
		Customs tariff number:	82054000

- Adjustable Kraftform torque screwdriver with pistol handle and Rapidaptor quick-release chuck
- Suitable for bits with 1/4" hex head drive
- Rapidaptor technology for rapid bit change
- Distinct signal when pre-set value is reached
- Numerical torque value indicator

Wera torque screwdriver. Kraftform pistol handle for particularly high torque transfer, multi-component for high working speeds and particularly ergonomic screwdriving. Variable torque setting option with highest precision. Simple adjustment of the required torque value without any special tools. Easy-to-read scale value. Rapidaptor quick-release technology for rapid bit change. Unlimited torque to loosen seized screws. Multi-component Kraftform handle with hard and soft zones for high working speeds, whilst being easy on the hand. Suitable for bits with 1/4" hexagon head drive as per DIN ISO 1173-C 6.3 and E 6.3 (ISO 1173).

Web link

https://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_variable_torque_adjustment_models_7400_pistole_inch.html

Wera - 7400 Pistole inch
05074712001 - 4013288102904


Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Adjustable Torque Screwdrivers



Wera's adjustable torque screwdrivers allow variable torque settings with maximum precision and ensure that the user gets the very best results in the familiar Wera design with superior ergonomics.

Simple setting




Simple setting of the required torque by hand.

Easy-to-read



Easy-to-read scale value.

Measurement accuracy



Measurement accuracy is $\pm 6\%$ (article 1430: $\pm 10\%$) in accordance with the standard DIN EN ISO 6789. Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.

Unlimited torque



Unlimited torque for loosening seized screws.

Versatile










Rapidaptor technology makes the tool adaptable since bits and sockets can be exchanged rapidly.

Rapid-in and self-lock



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

Further versions in this product family:

								
	art. no.	inch	in. lbs.	in. lbs.	mm	mm	inch	inch
05074712001	7447	1/4	25.0-55.0	2.5	150	100	6	4

Web link

https://products.wera.de/en/torque_tools_series_7400_kraftform_torque_screwdrivers_variable_torque_adjustment_models_7400_pistole_inch.html

Wera - 7400 Pistole inch
05074712001 - 4013288102904

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de