Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding 4-PLEX® Receptacles

HUBBELL

Features

- Surge supression with lights, 80 joules/6500A per mode
- Anchor hole and loop feature secures solid wire for fast, easy terminations
- Triple wipe contacts
- Easily accessible break-off tabs for split wiring
- Three conductors energize all four outlets

Ordering Information

Description	Device Color	UPC	Catalog Number
Surge suppression,	Blue	783585017877	HBL420S
4-PLEX receptacle			



Listed to UL Standard 498 File E2186 Certified to CSA 22.2, No. 42 File 285 NEMA® WD-6 Compliant

Specifications

Face	Polycarbonate	
Base	PBT	
Power Contacts	.032 in. (.8) Brass	
Ground Contacts	.031 in. (.8) Brass	
Ground Plate	.032 in. (.8) Plated Steel	

Performance

Electrical

Current Interrupting Capable of withstanding a fault level of 1000A, per UL498

Dielectric Voltage Withstands 2,000V minimum

Mechanical


Product Identification Ratings are a permanent part of the device
Terminal Accommodation #12 AWG stranded or solid copper conductor only
Terminal Identification Terminals identified in accordance with UL 498 and CSA

Environmental

Flammability UL 94 V-2

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)





Accessories

4-PLEX Adapter Plate	HBL4APBL	

Resources

Customer Use Drawing eCatalog

