

Straight Blade Devices

Accessories

For 15 and 20 Ampere, 125 and 250 Volts and 277 Volts AC Devices



Wallplates, 1-Gang

Description	Color	Duplex Receptacle	Style Line® Receptacle	Single Receptacle Plate 1.40 in. (35.6) Dia.
Thermoplastic, smooth.	Black	P8BK	P26BK	P7BK
	Brown	P8	P26	P7
	Gray	P8GY	P26GY	P7GY
	Ivory	P8I	P26I	P7I
	Light Almond	P8LA	P26LA	P7LA
	Orange	P8OR	-	-
	Red	P8R	P26R	P7R
	White	P8W	P26W	P7W
Stainless steel 302/304, .035 in. (0.9) horizontal brushed finish.		SS8	SS26	SS7
Brass .04 in. (1.0), horizontal brushed finish.		SB8	SB26	SB7
Aluminum .05 in. (1.3), horizontal brushed finish.		SA8	-	SA7



P8



P26I



SS7

Weatherproof Covers

Description	Duplex Receptacle	Single Receptacle Plate 1.40 in. (35.6) Dia.
RTP, gray, for FS/FD box mounting.	HBL5221	HBL7423WO
RTP, yellow, for FS/FD box mounting.	HBL52CM21	HBL74CM23WO
RTP, gray, for device mounting.	HBL5222	-
RTP, yellow, for device mounting.	HBL52CM22	-
Cast aluminum for FS/FD box mounting.	HBL5206WO	HBL7420
Cast aluminum for device mounting.	HBL5205WO	-

Note: All weatherproof plates are UL Listed for Wet Locations.
 Those with suffix WO are listed for use with cover open, all others with cover closed.
 RTP is an abbreviation for reinforced thermoplastic polyester.
 See section O for additional information on cover plates.



HBL52CM22



HBL5206WO



HBL7423WO

Dimensions in Inches (mm)