



Main

| | |
|-----------------------|---|
| Product Range | Legacy |
| Product Type | Socket |
| Product Compatibility | Relay 784XDX Suppressor module 70-ASMM Diode 70-ASMD Signalling device 70-ASMLG Suppressor module 70-ASMR |
| Number of Terminals | 14 |
| Switch Function | 4PDT |
| Contact Composition | 4 NO + 4 NC |

Complementary

| | |
|--------------------------------|---|
| Rated Current | 16 A |
| [Ue] rated operational voltage | 300 V |
| Contact Terminal Arrangement | Mixed |
| Connections Terminals | Output screw clamp terminalssolid Output screw clamp terminalsstranded |
| Tightening Torque | 0.9 N.m |
| Fixing Mode | By screw M3.5, M3.5 panel Clip-on 35 x 15 mm symmetrical DIN rail |
| Shape of Screw Head | Combination roundhead |
| Product Weight | 2.19 oz (62 g) |
| Width | 1.97 in (50 mm) |
| Depth | 3.13 in (79.6 mm) |

Environment

| | |
|---------------------------------------|-----------------------------|
| Ambient Air Temperature for Storage | -40...221 °F (-40...105 °C) |
| Ambient Air Temperature for Operation | -40...131 °F (-40...55 °C) |
| IP Degree of Protection | IP20 |
| Flame Retardance | UL94-V0 |
| Product Certifications | UL CSA CE |

Ordering and shipping details

| | |
|-----------------------|------------------|
| GTIN | 3606480278181 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 2.19 oz (62.0 g) |

Packing Units

| | |
|------------------------|------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 3.31 in (8.4 cm) |
| Package 1 width | 1.97 in (5 cm) |
| Package 1 Length | 1.18 in (3 cm) |
| Unit Type of Package 2 | BB1 |

| | |
|------------------------------|------------------------|
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 21.87 oz (620.0 g) |
| Package 2 Height | 3.37 in (8.55 cm) |
| Package 2 width | 2.42 in (6.15 cm) |
| Package 2 Length | 9.98 in (25.35 cm) |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 200 |
| Package 3 Weight | 27.34 lb(US) (12.4 kg) |
| Package 3 Height | 11.81 in (30 cm) |
| Package 3 width | 13.78 in (35 cm) |
| Package 3 Length | 17.32 in (44 cm) |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Approximate Dimensions

