



DUALIE® 3AA COLOR-RITE® INTRINSICALLY SAFE FLASHLIGHT WITH COLOR-RITE TECHNOLOGY®



Flood light produces a soft, wide Color-Rite beam to illuminate your work area and for color recognition

Material/Lens	Impact and chemical resistant Engineered Polymer resin; gasket-sealed and vented. Unbreakable polycarbonate facecap.
Dims/Weight	Length: 7.00 in. (17.78 cm) Facecap diameter: 1.86 in. (4.72 cm) Body thickness: 1.06 in. (2.69 cm) Body Width: 1.52 in. (3.86 cm) 6.6 oz. (187 grams) with AA alkaline batteries, 5.7 oz. (162 grams) with AA lithium batteries*
Light Source/ Output	One (1) high-power white LED, impervious to shock with a 50,000 hour lifetime. One (1) 90 CRI LED, impervious to shock with a 50,000-hour lifetime. Spot beam utilizes smooth parabolic reflector for tight beam with optimum peripheral illumination. Flood beam produces a soft, wide beam to illuminate your work area. Spot and flood beams intersect for an uninterrupted light pattern to eliminate blind spots. Features two white LEDs and three output modes: spot, flood, spot/flood combo: – Spot – 225 lumens, 8,000 candela peak beam intensity and 179 meter beam distance. – Flood – 175 lumens, 380 candela peak beam intensity and 39 meter beam distance. – Spot and Flood combined – 320 lumens, 7,000 candela peak beam intensity and 167meter beam distance.
Switch	Opposing head switches for easy identification. Spot LED push button head switch provides one handed momentary or constant operation. Flood LED push button head switch provides on/off operation.
Battery	Three (3) "AA" size alkaline or lithium primary batteries. Mechanical battery polarity protection.
Features	– IP67 - dust-tight; waterproof to 1m for 30 minutes; 2m impact resistance tested – One-handed operation of all lighting modes – Integrated, non-protruding spring-loaded belt clip contained within the body outline – Corrosion Proof
Approvals	Class I, II, Division 1, Groups A, B, C, D, E, F, G; Class III; CL I, ZN 0, IIC; Exia; T-Code: T4 Meets applicable European Community Directives
Warranty	Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction. Visit streamlight.com for full warranty information. Visit streamlight.com for full warranty information.

Description	UPC	Part #
Dualie 3AA Color-Rite - includes 3 "AA" alkaline batteries - Yellow	080926-68910-7	68910

68089
Poly Mount Kit universal mounting via slot
attachment or self-adhesive mount



Adheres to side of hard hat



Clips onto hard hats



68085



68086



99075



Description	UPC	Part #
4AA/3AA Helmet Mount	080926-68085-2	68085
4AA/3AA Gallet mount	080926-68086-9	68086
Poly Mount Kit	080926-68089-0	68089
Rubber Helmet Strap	080926-99075-3	99075