

# 86 03 150



## Mini Pliers Wrench pliers and a wrench in a single tool



- adjustable tightening tool
- also excellent for gripping, holding, pressing and bending workpieces
- replaces sets of spanners, both metric and imperial
- smooth jaws for damage free installation of plated fittings
- zero backlash jaw pressure prevents damage to edges of sensitive components
- adjustment at the touch of a button directly on the workpiece
- parallel jaws give a more solid grip; the construction gives infinite adjustment of all widths up to the specified maximum size
- reliable catching of the hinge bolt: no unintentional shifting
- the action of the jaws allows quick tightening and release of bolted connections using the ratchet principle
- lever transmission greater than 10 : 1 for strong gripping power
- Chrome vanadium electric steel, forged, oil-hardened
- the mini pliers wrench for precision mechanics
- ideal multi-purpose wrench in pocket size
- indispensable companion in emergency tool kit


The smooth jaws grip all parallel surfaces in the capacity range with a high degree of pressure if necessary and open up almost unlimited application possibilities for the pliers wrench: e.g. for tightening locknuts, exerting pressure to activate the adhesive power of contact adhesives, edge breaking in tile work, snapping cable ties, utilisation as a small vice.

<b>Article No.</b>	86 03 150
<b>EAN</b>	4003773069676
<b>Pliers</b>	nickel plated
<b>Handles</b>	plastic coated
<b>B2 mm</b>	7,0
<b>B3 mm</b>	10,5
<b>B1 mm</b>	4,7
<b>Adjustment positions</b>	14
<b>Capacities for nuts Inch</b>	1
<b>Capacities for nuts mm</b>	27
<b>Length mm</b>	150
<b>Net weight g</b>	175




Working on plated fittings without damage of the surface

Pliers wrench: zero backlash contact pressure, no damage to edges



Conventional open end wrench: edge pressure causes surface damage





Working using the ratchet principle



Fast adjustment by pushing a button

technical change and errors excepted



### Spare Parts

Article No.	EAN	
86 09 150	4003773073123	Range of spare parts adjustment for 86 150