

# 86 05 150 S02

## Pliers Wrench with roughened jaws



- e.g. for opening plastic cable connectors
- also excellent for gripping, holding, pressing and bending workpieces
- infinitely variable gripping of parallel surfaces up to the specified capacity by means of parallel jaws
- zero-backlash, full-surface contact
- roughened jaws for a better grip
- fast adjustment by pushing a button directly on the workpiece
- no unintentional shift of the gripping jaws and no slipping of the joint
- lever transmission greater than 10 : 1 for strong gripping power
- Chrome vanadium electric steel, forged, oil-hardened

<b>Article No.</b>	86 05 150 S02
<b>EAN</b>	4003773071785
<b>Pliers</b>	nickel plated
<b>Handles</b>	handles with multi-component grips
<b>B2 mm</b>	7,0
<b>B3 mm</b>	10,5
<b>B1 mm</b>	4,7
<b>Adjustment positions</b>	14
<b>Capacities for nuts Inch</b>	1
<b>Capacities for nuts mm</b>	27
<b>Length mm</b>	150
<b>Net weight g</b>	193

technical change and errors excepted

### Spare Parts

<b>Article No.</b>	<b>EAN</b>	
86 09 150	4003773073123	Range of spare parts adjustment for 86 150