

# 99 10 300

## High Leverage Concretors' Nipper high lever transmission



- for fixing Monier iron in place with tie wire from a roll
- Wire is twisted and cut in a single pass.
- high-leverage joint, minimising strain, even when thick binding wires are used
- very slim shape for tying submerged positioned steel rods
- The high damping of the cutting stroke on cutting through the tie wire reduces the strain on tendons and muscles.
- Cutting edges with additional hardness; cutting edge hardness approx. 61 HRC
- High-grade special tool steel, forged, oil-hardened

compared to conventional concretors' nippers of the same size.

<b>Product Number</b>	99 10 300
<b>EAN</b>	4003773022398
<b>Pliers</b>	black atramentized
<b>Head</b>	polished
<b>hard wire Ø mm</b>	2
<b>medium hard wire Ø mm</b>	3,8
<b>Head width mm</b>	25
<b>Length mm</b>	300
<b>Net weight g</b>	501



*technical change and errors excepted*

