

CADDY® TPC TUBE AND PIPE CLAMP

CADDY® TPC

- Quick positioning of pipe and tube
- Clamps any pipe, tube, conduit or wire from 3/8" OD through 2-3/8" OD
- Strong, UV resistant Nylon 66 works as an insulator
- Releasable locking mechanism
- Perfect for jobs where many different pipe and tube sizes are used
- Permits horizontal and vertical positioning of pipe/tube



Install the TPC onto the CADDY TSGB for an adjustable pipe bracket and clamping system!



1 Break the TSGB and assemble



2 Position bracket and mark pipe locations



3 Screw the TPC base on to the TSGB where marked in Step 2



4 Install the TSGB to wall studs



5 Secure the pipe by attaching TPC retainer



CADDY TPC TUBE AND PIPE CLAMP



The patented design of the TPC clamp, when used with the CADDY TSGB bracket, offers a unique, time-saving solution for tube/pipe positioning. ERICO has teamed up with Sioux Chief to provide this new solution.

Features:

- Wide temperature range: -10°F through +130°F
- Pilot holes in bracket permit easy attachment with screwdriver
- Innovative clamp design permits horizontal and vertical positioning of pipe/tube
- Strong, UV resistant Nylon 66 reduces vibration and noise and works as an insulator
- Clamp can be used for indoor and outdoor applications
- Clamps any pipe, tube, conduit or wire from 3/8" through 2-3/8" OD
- Releasable locking mechanism

The adjustable TSGB fits typical or variable stud spacing.



UPC#	Catalog Number	Description
782856		
47616	TSGB16	16" adjustable screw gun bracket
47624	TSGB24	24" adjustable screw gun bracket
45865	TPC112	Tube and pipe clamp 3/8" thru 1-1/8"
45866	TPC238	Tube and pipe clamp 5/8" thru 2-3/8"
45867	TSGB16112	Kit - includes (25) 16" adjustable screw gun bracket & (50) TPC112
45868	TSGB24112	Kit - includes (25) 24" adjustable screw gun bracket & (50) TPC112

FASTENING PRODUCTS CUSTOMER SERVICE

Mechanical Division
Phone: 800-333-0852
Fax: 800-677-5403

ERICO®
www.erico.com