IBC 2000i™

INTERMEDIATE BULK CONTAINMENT MADE EASY.

ENPAC's® integrated IBC 2000i™ gives intermediate bulk container users more versatile spill containment. It fits more than 99% of all IBC dispensing units and features a large sump capacity of 385 gallons; more than exceeding EPA 40 CFR 264.175 regulations. The unit also comes with an integrated 5-gallon pail holder for quick and easy dispensing.

The IBC 2000i™ is the only one-piece, light weight, 100% polyethylene IBC spill containment unit that is forkliftable and nestable for convenient shipment and storage and it reduces shipping costs. The polyethylene construction will not rust, corrode, or have adverse reactions with chemicals. Optional drain.







Tarps include:

- Fold up working area
- Document pouch
- Durable pockets for weighted corners in harsh weather
- Adjustable corner-cinch bungees

(see Tarp on page 13)

IBC 2000i™

Part #	Description	Pedestal Dimension in. (cm)	Ext. Dimension in. (cm)	Weight lb. (kg)	Spill Cap. gal. (L)	Load Cap. lb. (kg)
5469-YE 5469 YE-D	2000i (w/drain)	56.75 x 56.75 x 29.5 (144 x 144 x 75)	73 x 80.5 x 29.5 (185 x 204 x 75)	291.1 (132)	385 (1,457)	8,000 (3,629)
5469-TARP	Tarp		76 x 80 x 73.75 (183 x 203 x 187)	14.6 (6.6)		

Regulations: EPA 40 CFR 264.175, SPCC, NPDES and UFC



IBC SPACE-SAVER™

Small footprint takes up minimal floor space! Floor space efficient alternative for storing, dispensing and containing IBC totes up to 275-gallons. With features like a solid polyethylene construction for high chemical compatibility and a rugged, easily-removable integrated platform; drips, leaks and spills don't stand a chance!



(see Tarp on page 13)

IBC SPACE-SAVER™

Part #	Description	Ext. Dimension L x W x H in. (cm)	Weight lb. (kg)	Spill Cap. gal. (L)	Load Cap. lb. (kg)
5460-YE 5460-YE-D	Space-Saver (w/drain)	57 x 57 x 47 (145 x 145 x 119)	245 (111)	275 (1,041)	3,000 (1,360)
5460-TARP	Tarp	60 x 60 x 50 (153 x 153 x 55)	11 (4)		

Regulations: EPA 40 CFR 264.175, SPCC, NPDES and UFC