



MAKE YOUR MARK

LONG TAPE MEASURES

FLT SERIES

Features an ergonomically designed housing handle with tactile rubber grip for balance and comfort. Includes a freewheeling hub for fast pay out of blade without spinning crank. Massive crank arm with large, easy-grip knob for comfort and reliability. Knob folds down for storage. Locking pawl enables proper blade tension during measurement.



FLT18165

Limited lifetime warranty.


MODEL	UPC (052837)	LENGTH	UNITS	ZERO PT.	ATTACHMENT	BLADE (page 23)
FLT18165	027170	165 ft.	ft, in, 1/8	Hook End	Hook	F1
FLT10165	027187	165 ft.	ft, 1/10, 1/10	Hook End	Hook	F2
FLT18M165	027163	165 ft./200m	ft, in, 1/8 & m, cm, 2mm	Hook End	Double Hook	F1 & F13
FLT18200	027156	200 ft.	ft, in, 1/8	Hook End	Hook	F1
FLT10200	027132	200 ft.	ft, 1/10, 1/10	Hook End	Hook	F2
FLT1810200	027316	200 ft.	ft, in, 1/8 & ft, 1/10, 1/100	Hook End	Double Hook	F1 & F14
FLT18M200	026142	200 ft./60m	ft, in, 1/8 & m, cm, 2mm	Hook End	Double Hook	F1 & F13
FLT50MM	027194	50m	m, cm, 5mm & m, cm, 2mm	Hook End	Hook	F12 & F13

AVAILABLE IN

F = 1/2-inch wide, fiberglass, long tape



F1 = Hook, Zero = Hook end, SAE ft., in., 1/8



F2 = Hook, Zero = Hook end, ENG: ft., 1/10, 1/100



F13 = Hook, Zero = Hook end, Metric (YELLOW): cm, mm



F14 = Hook, Zero = Hook end, ENG (YELLOW): ft., 1/10, 1/100

FLT Series Long Tape Sell Sheet