



MAKE YOUR MARK

SHORT TAPE MEASURES

MAGNETIC TIP

The magnetic hook end sticks to any metal surface. Stick it to a metal door frame and you can pace off 10 feet or more. Great for drop ceiling work, steel framing, HVAC, and shop work.



PG1825MAG

HV PG1825ALVMAG

HV = High Visibility Option

FEATURE	DEFINED	RATING
Lock*	Slide	●●●●○
Case & Components	Chrome-Coated ABS	●●●●○
Blade	Nylon-Coated Steel	●●●●○
Impact Durability		●●●●○

Overall: 4.00 *The Chrome model is 3.75 overall, the lock is not as powerful as the Autolock version models.

Limited warranty.

MODEL	UPC (052837)	LENGTH	UNITS	WIDTH (in.)	STAND OUT (ft.)	BLADE (page 31)
PG1825MAG	027521	25 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	1	up to 8	B9
PG1825VMAG	027828	25 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	1	up to 8	B9
PG1825ALVMAG	027811	25 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	1	up to 8	B9

AVAILABLE IN

B = 1-inch wide, 2x nylon-coated, short tape



B9 = Magnet, SAE: ft., in., 1/8, 1/16 (1/32 in. first ft.)

Magnetic Tip Series Short Tape Sell Sheet