

PIG® Roof Leak Diverter Bucket Kit with Absorbents

#TLS668 - 7' x 7'



Our portable Leak Diverter Bucket Kits are perfect for grab-and-go response to overhead leaks.

- Contains supplies for rapid response to roof leaks, all in a 6.5-gallon pail
- Pail can be used as a collection container for diverted liquid; printed "Caution" message doubles as a warning sign
- Nonpermeable tarp is vinyl coated for strength and durability; resists punctures, UV and mildew for long life
- Hangs easily in problem spots to catch nuisance leaks and channel them to a floor drain or collection container
- Flow rate of 3.33 gallons per minute when used with a 1/2" ID hose
- Translucent material lets light through and allows easy monitoring of leak
- Preinstalled quick connect set lets you attach hose to leak diverter in seconds
- Adjustable straps allow fast setup and response
- High-visibility yellow PIG Mat Pads soak up puddles to keep floors safe; "Caution" message draws attention to spill
- PIG All-Purpose Wipers are great for wiping down diverter kit before storage or for cleaning up small spills
- Need a custom size or solution? Just call 1-800-HOT-HOGS (468-4647)



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: TLS668 - Pg 1 of 3

TLS668 Specifications

Use With:	Roofs
Drainage Hose Included:	Yes
Flow Rate:	3.33 gal. per Minute
Grommets/D-Rings:	4 Grommets
Hanging Straps Included:	Yes
Hose Connector:	.75" w/ Quick Connect
Installation Method:	Hanging Straps
Thickness:	16 mil
Sold as:	1 each
# per Pallet:	32
Composition:	Leak Diverter - 67% PVC, 33% Polyester Hose - PVC Straps - Nylon Bucket - Plastic Mats - Polypropylene
Includes:	1 - 7' L x 7' W Leak Diverter 1 - 25' L Drainage Hose 4 - 60" L Adjustable Hanging Straps 1 - 6.5 gal. Bucket 1 - 30 Pack "CAUTION" PIG® Mat Pads 2 - 25 Pack PIG® All-Purpose Wipers
UNSPSC:	24141506

Technical Information

Warnings & Restrictions:

Chemical Resistance
Limited chemical-resistance; not suitable for temperatures over 190° F/88° C.

Technical Documents:

(Available at newpig.com)

Product Data Sheet (PDS)

Safety Data Sheet (SDS)

Chemical Compatibility (CCG)



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: TLS668 - Pg 3 of 3