

PIG® Pipe Leak Diverter

#TLS248 - 18" x 18"



Purpose-built design catches pipe leaks or condensation to protect equipment, inventory and personnel.

- Hangs from a leaking pipe to catch nuisance leaks and channel them to a floor drain or collection container
- Nonpermeable tarp is vinyl-coated for strength and durability; resists punctures, UV and mildew for long life
- Built-in grommets and included rubber straps make it easy to hang from an overhead pipe
- Choose yellow for high visibility, gray to blend with plant ceilings or clear to monitor leaks
- Flow rate of 3.33 gallons per minute when used with a 1/2" ID hose
- Need a custom size or solution? Just call 1-800-HOT-HOGS (468-4647)



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: TLS248 - Pg 1 of 3

TLS248 Specifications

Use With:	Pipes
Drainage Hose Included:	No
Flow Rate:	3.33 gal. per Minute
Grommets/D-Rings:	4 Grommets
Hanging Straps Included:	Four 14" L
Hose Connector:	.75"
Installation Method:	Hanging Straps
Thickness:	Clear - 13 mil, Colors - 16 mil
Sold as:	1 each
# per Pallet:	192
Composition:	Leak Diverter (Colors) - 67% PVC, 33% Polyester Leak Diverter (Clear) - PVC w/ Polyester Reinforcement Straps -Rubber
UNSPSC:	24141506

Technical Information

Warnings & Restrictions:

Chemical Resistance
Limited chemical-resistance; not suitable for temperatures over 190° F/88° C.

Technical Documents:

(Available at newpig.com)

Product Data Sheet (PDS)



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: TLS248 - Pg 3 of 3