

NYLON - BRAID

DIAMETER			LENGTH		AVG BREAK	LINEAR DENSITY		WEIGHT	
IN	MM	CIRC	FT	M	STRENGTH	LBS/100'	KTEX	LBS	KG
1/2"	12	1 1/2"	500'	152.4	3960	5.40	80.38	27.0	12.25