

PROTO® MINIATURE PLIERS & CLAMPS



J292WRXL



J293XL



J286LNXL



J269XL

- Small in size for delicate and fine work.
- Made of quality alloy steel for long life.
- High corrosion resistant finish with welding spatter resistance.
- Precisely machined teeth for a positive grip and to help prevent slippage.
- Locking mechanism helps leave both hands free when clamping, helping to eliminate squeezing action and general hand fatigue when manipulating. Also helps to save time in repetitive jobs.
- Tip of release lever projects at end of handle for a safe, quick, no-pinch, powerful release especially when tools are firmly locked.
- Spring loaded release lever is out of the way when handling.
- Drop forged jaws and rugged tooth profile for durability and toughness.
- Holes in mobile jaw are drilled and not press punched to ensure they are cylindrical to ensure maximum bearing with rivets. (Punched holes tend give poor bearing.)
- Large diameter of rivets to help permit secure joints adding to the durability and robustness of the tools.
- Piano wire spring for smooth and efficient jaw opening.

PROTO MINIATURE CURVED JAW PLIERS

- Narrow large opening curved shaped jaws.
- Allows firm hold on all round shapes.
- Universal tool for multi-use.

PROTO MINIATURE CURVED PLIERS w/ CUTTERS

- Two tools in one. Cuts MIG wire, copper and steel.
- Use for fine applications, jewelry assembly and repair work.

PROTO MINIATURE STRAIGHT JAW PLIERS

- For laboratory and surgical work.

PROTO MINIATURE LONG NOSE PLIERS

- Long slim jaw design allows accessibility into recessed areas.
- For fine auto service jobs.

PROTO MINIATURE C-CLAMPS

- For handicrafts.

PROTO MINIATURE C-CLAMPS w/ SWIVEL PADS

- Knurled swivel pads- Allow non-slip no damage parallel clamping even on tapered surfaces.
- For electronics.

Product SKU No.	Description	UIC	Length	Jaw Opng.	Jaw Wdth.	Jaw Depth	Jaw Wght. Hght. (lbs.)	Jaw Hrdnss
J290XL	Proto Mini. Curved Jaw Pliers 7-15/32"	662679997083	7-15/32"	1-21/32"	11/32"	1-19/64"	— 0.82	49-53
J292WRXL	Proto Mini. Curved Pliers. w/Cutters 9-4/11"	662679997113	9-4/11"	2-23/64"	1/2"	1-1/2"	— 1.32	49-53
J293WRXL	Proto Mini. Curved Pliers w/Cutters 5-1/2"	662679997137	5-1/2"	1-19/64"	21/64"	55/64"	— 0.40	49-53
J294WRXL	Proto Mini. Curved Pliers w/Cutters 7-15/32"	662679997144	7-15/32"	1-21/32"	11/32"	1-11/64"	— 0.82	49-53
J291XL	Proto Mini. Straight Jaw Pliers 7-15/32"	662679997151	7-15/32"	1-21/32"	1/2"	1-1/2"	— 0.88	49-53
J293XL	Proto Mini. Straight Jaw Pliers 9-1/4"	662679997120	9-1/4"	2-23/64"	5/8"	1-21/32"	— 1.39	49-53
J286LNXL	Proto Mini. Long Nose Pliers 6-10/11"	662679997069	6-10/11"	2-5/32"	5/16"	1-31/32"	— 0.42	48-51
J265XL	Proto Mini. C-Clamps 6-8/11"	662679997045	6-8/11"	2-23/64"	5/16"	1-61/64"	2-7/16" 0.53	—
J266XL	Proto Mini. C-Clamps 11-1/5"	662679997052	11-1/5"	3-15/16"	15/32"	3-45/64"	4-11/64" 1.96	—
J269XL	Proto Mini. C-Clamps w/Swvl Pds. - 6-1/2"	662679997267	6-1/2"	1-61/64"	3/4"	1-61/64"	— 0.6	—
J270XL	Proto Mini. C-Clmps w/Swvl. Pds. - 12-19/32"	662679997274	12-19/32"	3-9/64"	1-11/64"	3-45/64"	— 2.2	—

