## Architectural Programmable Wall Heater



**Four colors to choose from:**Bronze, Navajo White, Aluminum and Northern White

- ► 5 DAY / 2 DAY PROGRAMMING
- **► BUILDING MANAGEMENT SYSTEM CONNECTION**
- **► SECURITY LOCKOUT FUNCTION**
- ► 'RIGHT OUT OF THE BOX' SET-UP
- ► PREMIUM HEAVY-DUTY CAST ALUMINUM GRILLE
- ► APPLICATIONS INCLUDE:
  - RESTAURANTS
  - HOTELS
  - CONFERENCE ROOMS
  - ATRIUM
  - RESIDENTIAL
  - ... AND MUCH MORE













# OUTSMART THE COMPETITION




### **SELECTION CHART**

| CATALOG            |                 |  |             | MAX  | MAX    |
|--------------------|-----------------|--|-------------|------|--------|
| NUMBER             | UPC             | VOLTS  | WATTS       | AMPS | BTUHR  |
| SSAR1802           | 6 85360 15683 5 | 120  | 540 - 1800  | 15   | 6,142  |
| SSAR4808           | 6 85360 15675 0 | 208  | 1800 - 4800 | 23.1 | 16,378 |
| SSAR4804           | 6 85360 15678 1 | 240  | 1800 - 4800 | 20.0 | 16,378 |
| SSAR4807           | 6 85360 15679 8 | 277  | 1800 - 4800 | 17.3 | 16,378 |
| SURFACE MOUNTING F | RAMES           |  |             |      |        |
| HTWHSM             | 6 85360 15545 6 | Surface Mounting Frame 16-1/4" W x 19-3/8" H x 3-7/8" D    |             |      |        |
| HTWHS1             | 6 85360 15548 7 | 1" Semi-Recess Mounting Frame 16-1/4" W x 19-3/8" H x 1" D |             |      |        |
| HTWHS2             | 6 85360 15551 7 | 2" Semi-Recess Mounting Frame 16-1/4" W x 19-3/8" H x 2" D |             |      |        |


Note: Standard grille color is northern white.

Add W (Navajo White), AL (Aluminum) or BZ (Bronze) suffix to catalog number. Example: SSAR4008W. Allow two weeks delivery for models with special color. See Color Selection Chart for custom colors.


#### THERMOSTAT DISPLAY



#### **DIMENSIONS**



15.85"



#### **FEATURES**

- 100% Energy Efficient heater automatically adjusts wattage output
- ► 5 day / 2 day Programming
- Security Lockout feature
- ► Unique Styling No other heater in the market comes close to the unique styling of the SmartSeries®
- Fan only mode (no heat) for supplemental ventilation
- On / Off switch
- BMS feature allows connection to Building Management Systems (Dry contact)
- ► Easy to use LCD touch screen, with night light feature
- Remote control to make adjustments anywhere in the room
- ▶ 2-piece construction for easy installation
- Precise heat output within 1.5°F of set temperature
- ► Thermostat range 40°-99°F (4°-37°C)
- ► 5-Year Element Warranty

#### **MOUNTING LIMITATIONS**

Do not install heater closer than 12" to the floor, 12" to an adjacent wall, 36" to the ceiling. Do not install heater behind towel rack or door, upside down or sideways, in the floor, in the ceiling, or in closets.