







	HEAVY-DUTY UTILITY CART 9T SERIES		HEAVY-DUTY UTILITY CART 89 SERIES		HEAVY-DUTY UTILITY CART 89 SERIES		TRADES CART		HEAVY-DUTY UTILITY CART 88 SERIES		HEAVY-DUTY UTILITY CART 00 SERIES	
												
SMALL	500 LBS.	34.25" (L) X 17.38" (W) X 31.5" (H)	500 LBS.	39.0" (L) X 17.9" (W) X 33.25" (H)	500 LBS.	37.9" (L) X 19.2" (W) X 33.3" (H)	330 LBS.	38" (L) X 19.3" (W) X 33.4" (H)	500 LBS.	39.0" (L) X 17.9" (W) X 33.3" (H)	500 LBS.	37.9" (L) X 19.25" (W) X 33.3" (H)
MEDIUM	500 LBS.	40.25" (L) X 25.6" (W) X 32.5" (H)	500 LBS.	42.25" (L) X 25.9" (W) X 33.25" (H)	500 LBS.	43.9" (L) X 25.9" (W) X 33.3" (H)	-	-	500 LBS.	44.0" (L) X 25.3" (W) X 33.3" (H)	500 LBS.	44.0" (L) X 25.9" (W) X 33.3" (H)
LARGE	-	-	-	-	-	-	-	-	750 LBS.	55.0" (L) X 25.9" (W) X 33.3" (H)	500 LBS.	54.0" (L) X 25.3" (W) X 36.0" (H)
AVAILABLE COLORS	BLACK		BLACK, BEIGE		BLACK, BEIGE		BLACK, RED		BLACK, BEIGE		BLACK, BEIGE	
HANDLE STYLE	FLAT-HANDLE		FLAT-HANDLE		FLAT-HANDLE		FLAT-HANDLE		ERGO-HANDLE		ERGO-HANDLE	
TOP-SHELF STYLE	POCKET-SHELF		POCKET-SHELF		FLAT-SHELF		FLAT-SHELF		POCKET-SHELF		FLAT-SHELF	
BOTTOM-SHELF STYLE	POCKET-SHELF		POCKET-SHELF		POCKET-SHELF		POCKET-SHELF		POCKET-SHELF		POCKET-SHELF	
MATERIAL	POLYPROPYLENE (PP)		POLYPROPYLENE (PP)		POLYPROPYLENE (PP)		POLYPROPYLENE (PP)		POLYPROPYLENE (PP)		POLYPROPYLENE (PP)	
CASTER OPTIONS	TPR QUIET, NON-MARKING		TPR QUIET, NON-MARKING		TPR QUIET, NON-MARKING		TPR QUIET, NON-MARKING		TPR / PNEUMATIC QUIET, NON-MARKING		TPR / PNEUMATIC QUIET, NON-MARKING	
CASTER SIZE	5" OR 8" (SOLD SEPERATELY)		5" OR 8" (SOLD SEPERATELY)		5" OR 8" (SOLD SEPERATELY)		5"		5" OR 8" (SOLD SEPERATELY)		5" OR 8" (SOLD SEPERATELY)	
EASY-REACH TOOL/ACC. STORAGE COMPARTMENT			•		•		•		•		•	
BUILT-IN TOOL HOLSTER & CADDY									•		•	
MOLDED-IN FITTINGS (FOR PIPES/RODS)									•		•	
INTEGRATED V-NOTCH									•			
BUILT-IN CORD WRAP					•		•					
ACCESSORIES												
REFUSE BIN (8 GALLON)					•		•					
UTILITY BIN (4 GAL.)					•		•					
CORD/STEP LADDER HOOKS	•		•		•		•		•		•	
3-OUTLET POWER STRIP	•		•		•		•		•		•	
FULL EXTENSION SLIDING DRAWER			•		•		•		•		•	

	STANDARD CASTERS		HEAVY-DUTY CASTERS		CASTER OPTIONS	
CASTER TREAD MATERIAL	TPR (THERMOPLASTIC RUBBER)		TPR (THERMOPLASTIC RUBBER)		PNEUMATIC	
CASTER SIZE	5"		5"		8"	
CASTER TYPE (QTY.)	2 SWIVEL; 2 FIXED		2 SWIVEL; 2 FIXED		2 SWIVEL; 2 FIXED	
LOCKING	NO		NO		NO	
WEIGHT-LOAD RATING	500 LBS		750 LBS		750 LBS	
FLOOR SURFACES	EXCELLENT	ASPHALT, BRICK, CARPET, CONCRETE, LINOLEUM/TILE, TERRAZZO, AND WOOD	ASPHALT, BRICK, CARPET, CONCRETE, LINOLEUM/TILE, TERRAZZO, AND WOOD	ASPHALT, BRICK, CARPET, CONCRETE, LINOLEUM/TILE, TERRAZZO, STEEL (RIBBED AND SMOOTH), AND WOOD		
	GOOD	STEEL (RIBBED AND SMOOTH)	STEEL (RIBBED AND SMOOTH)	-		
	FAIR	-	-	-		
OPERATING CONDITIONS	EXCELLENT	METAL SCRAPS (SMALL OR LARGE)	METAL SCRAPS (SMALL OR LARGE)	-		
	GOOD	WATER, STEAM, OR ANIMAL FATS	WATER, STEAM, OR ANIMAL FATS	MILD OR HARSH CHEMICALS, METAL SCRAPS (SMALL OR LARGE), WATER, STEAM, OR ANIMAL FATS		
	FAIR	MILD OR HARSH CHEMICALS, OIL & GREASE	MILD OR HARSH CHEMICALS, OIL & GREASE	OIL & GREASE		
REPLACEMENT ITEM #	3485097 - 5" TPR CASTER KIT SWIVEL: FG4501L20000 RIGID: FG4501L10000		SWIVEL: FG4546L10000 RIGID: FG4501L10000		FG4592000000	
ADDITIONAL INFORMATION	TPR CASTERS ABSORB SHOCK AND PROVIDE FLOOR SURFACE PROTECTION AND QUIET OPERATION. CHEMICAL AND WATER RESISTANT.		TPR CASTERS ABSORB SHOCK AND PROVIDE FLOOR SURFACE PROTECTION AND QUIET OPERATION. CHEMICAL AND WATER RESISTANT.		PNEUMATIC CASTERS PROVIDE A CUSHIONED AND QUIET RIDE FOR FRAGILE LOADS. ALSO IDEAL FOR ROUGH, UNEVEN SURFACES BOTH IN INDOOR AND OUTDOOR USE.	

HEAVY-DUTY UTILITY CARTS SELECTION GUIDE

To see our complete range of material handling solutions visit our online catalog at rubbermaidcommercial.com

RCP-384
#141734
©2015 Rubbermaid Commercial Products LLC
8900 Northpointe Executive Drive, Huntersville, NC 28078

