

EASY ON, CLEAN RELEASE

STUCCO MASKING TAPES

Thorough preparation is a requirement of your job – it's what helps you leave your mark of excellence on a job well done. You demand a tape that's easy to apply, yet strong enough to stand up against the harsh scraping of your trowel. You don't have time to waste cleaning up residue left behind after the tape has been removed. It's why you count on the Shurtape® line of stucco masking tapes for your stucco work.

Shurtape stucco masking tapes are designed with you in mind. Engineered to meet the rigid requirements of stucco applications, our full range of stucco masking tapes provides a secure, watertight seal, no matter the surface you're masking. Conformable to vinyl trim work, doors, windows, garage doors and more, our tapes are highly visible, as well as easy to unwind and tear. When the work is done, our tapes release easily and cleanly, even after prolonged exposure to sunlight.

Whether you're using a one-, two- or three-step process, Shurtape offers a broad array of stucco masking tapes to fit your needs.










STUCCO

SHURTAPE.COM 1.888.442.TAPE

Shurtape®
TRUE TO YOUR WORK™

EASY ON, CLEAN RELEASE

STUCCO MASKING TAPES

			Tensile	Adhesion to Stainless Steel	Thickness	Elongation	Service Temperature Range
PC 567		Specialty/outdoor UV grade cloth duct tape <ul style="list-style-type: none"> Removes cleanly up to 14 days UV resistant for outdoor use Protects surfaces when pressure washing and applying stucco Conformable to most surfaces 	21 lbs/in width	56 oz/in width	8 mils	17%	50 -200 F
PC 622		Premium grade cloth duct tape <ul style="list-style-type: none"> Waterproof backing High tensile strength Conformable to most surfaces Excellent holding power 	34 lbs/in width	56 oz/in width	12 mils	14%	50 -200 F
PC 667		Specialty grade cloth duct tape 14-day UV resistant <ul style="list-style-type: none"> Waterproof backing Easy tear Clean removal, no residue after 14-day exposure High tack Excellent UV resistance 	22 lbs/in width	50 oz/in width	9 mils	15%	50 -200 F
PC 668		Premium specialty grade cloth duct tape 14-day UV resistant <ul style="list-style-type: none"> UV inhibitors in the film eliminate residue, reducing clean-up time and expense Straight tear along width and length Aggressive adhesive holds strong to dusty surfaces White, waterproof backing significantly reduces heat absorption 	27.5 lbs/in width	70 oz/in width	11 mils	15%	50 -200 F
PE 333		Serrated edge, non-UV stucco masking tape <ul style="list-style-type: none"> Masking windows and doors in stucco applications Serrated edge makes product hand tearable Maintains a watertight seal Clean removal 	19 lbs/in width	70 oz/in width	7 mils	80%	32 -160 F
PE 444		UV resistant polyethylene film tape <ul style="list-style-type: none"> UV resistant Maintains a watertight seal Clean removal 	19 lbs/in width	80 oz/in width	7 mils	76%	32 -160 F
PE 555		UV resistant polyethylene film tape <ul style="list-style-type: none"> Waterproof Color-coding Splicing and seaming on pipe fitting covers 	27 lbs/in width	92 oz/in width	9 mils	94%	32 -160 F



SHURTAPE.COM
1.888.442.TAPE



Shurtape®

TRUE TO YOUR WORK™

ISO 9001 CERTIFIED QUALITY SYSTEM © 2014 Shurtape Technologies, LLC
Printed in USA on recycled paper. Form #SS-STUCCO-08/26/2014-P500