



Technical Characteristics

Socket Rating (CSA)	10A@300V
Approvals	UL Recognized Component - CSA Certified - CE Marked
Socket Rating (UL)	10A@600V - 15A@300V
Mounting Type	Panel or DIN Rail
RoHS Compliant	Yes
Number of Pins	8 Pin
Standard Quantity	1
Socket Type	Single Tier
Terminal Type	Screw Clamp
Type	N
For Use With	8501KP(D)12, KA81, KA82 Relays, 8430MPS (240V) Phase Loss Relays, 9050JCK11-19, 31-39, 51-59, 60, 1F, 3F and 5F Timers
Type of Pins	Tubular

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.