





PolyTac® LED Tactical Light

FL 1 STANDARD	POLYTAC LED
	130 LUMENS
	3h
	144m
	5200cd



Compact and lightweight, the Streamlight PolyTac LED is a lithium-powered flashlight with super-bright C4® LED technology. A tail-cap switch facilitates single-handed operation. Durable, waterproof construction ensures continued use in many different extreme conditions.

Material/Lens High impact super tough nylon polymer for exceptional durability and a sure grip. All openings o-ring sealed for weather resistance. Available in black, coyote or yellow. Borofloat glass lens, o-ring sealed.

Dims/Weight Length: 5.22 in. (13.3 cm) Major Diameter: 1.25 in. (3.18 cm) Body Diameter: 1.00 in. (2.54 cm)
4.1 oz (116 grams)

Light Source C4 LED technology, impervious to shock with a 50,000 hour lifetime

Switch Push-button tail switch for one-handed operation

Battery Two 3V CR123A lithium batteries (included)

Features • IPX7 rated design; waterproof to 1 meter for 30 minutes.

Approvals Most models meet applicable European Community Directives
Meets requirements of NFPA 1971-8.6 (2007)

Warranty Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. **THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW.** You may have other specific legal rights which vary by jurisdiction.

Item		UPC	Part #
PolyTac LED with lithium batteries. Blister Packaged.	Black	080926-88850-0	88850
PolyTac LED with lithium batteries. Blister Packaged.	Coyote	080926-88851-7	88851
PolyTac LED with lithium batteries. Blister Packaged.	Yellow	080926-88853-1	88853

The Streamlight Poly Mount conveniently attaches the PolyTac LED to a helmet and features a curved interface for fully adjustable positioning of the flashlight beam. Includes a slot adapter and an adhesive mounting option.



Helmet not included



Helmet not included



Item		UPC	Part #
Nylon holster		080926-85905	85905
Deluxe nylon holster		080926-85909	85909
Flip Lens	Red	080926-69115-5	69115
Flip Lens	Blue	080926-69116-2	69116
Flip Lens	Green	080926-69117-9	69117
Flip Lens	IR	080926-69118-6	69118
Rubber helmet strap		080926-99075-3	99075
Polymount Kit		080926-68089-0	68089
Lithium batteries (2) Pack		080926-85175-7	85175
Lithium batteries (12) Pack		080926-85177-1	85177
Lithium batteries (400) Pack		080926-85179-5	85179
Lithium batteries (6) Pack		080926-85180-1	85180



STREAMLIGHT



30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax
www.streamlight.com ©Streamlight, Inc. PolyTac LED 7/13