

ProTac® HL™ High Lumen Professional Tactical Light

FL1 STANDARD	HIGH	LOW
	600 LUMENS	33 LUMENS
	1h 15min	18h
	253m	57m
	16,000cd	800cd



Strobe runs 2.5 hours

Case Material: 6000 Series machined aircraft aluminum with anodized finish.

Dimensions/Weight: Length: : 5.40 in. (13.72 cm) Barrel Diameter: 1.0 in. (2.54 cm) Head Diameter: 1.375 in. (3.49 cm) Tri-Lobe Diameter: 1.45 in. (3.68 cm)
5.6 oz (158 grams) with batteries

Lens: Tempered glass lens, o-ring sealed

Light Source: C4® LED technology, impervious to shock with a 50,000 hour lifetime

On/Off: Multi-function, push-button tactical tailswitch facilitates one-handed operation of momentary, variable intensity or strobe mode. TEN-TAP™ programmable switch allows user selection of one of three different programs: high/strobe/low (factory default), high only, or low/high.

Battery: Two 3V CR123A lithium batteries (included)

Features: IPX7; waterproof to 1 meter for 30 minute; 1 meter impact resistance tested
LED Solid State Power Regulation provides maximum light output throughout battery life
TEN-TAP™ programmable switch allows user to select one of three different programs
Anti-roll facecap
Removable pocket clip
Nylon holster included
Serialized for positive identification

Approvals: Meets applicable European Community directives

Warranty: Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Item	UPC	Part #
ProTac HL with white LED Black	080926-88040-5	88040

Made in China



TEN-TAP™ Programming for Flexible Lighting Options



Streamlight makes our flashlights for a wide variety of applications, but we understand that not everyone wants the same lighting options. Do you like most of the features of a flashlight, but not the pre-set programs? Now, with our TEN-TAP™ Programming, you can reprogram the light from the standard default option. Reprogramming is easy and can be done from anywhere — with just a few quick taps of the switch you can change the lighting to fit your needs and how you'll be using it.

With those lights that feature TEN-TAP™ Programming, you can choose from the following three user-selectable programs:

- 1.High/Strobe/Low (factory default)
- 2.High only
- 3.Low/High

General Operation

Some Streamlight flashlights, such as the ProTac HL, feature a programmable switch with momentary operation (light press or tap) and constant on operation (press until click). The light is shipped from the factory in the default High-Strobe-Low program.

To turn on each lighting mode within this program:

- High: Tap and hold; click to lock on; click again for off.
- Strobe: Fast double-tap (within 0.4 seconds) and hold; click to lock on; click again for off.
- Low: Fast triple-tap (within 0.4 seconds per tap) and hold; click to lock on; click again for off.

Accessing Other Programs

With lights featuring the TEN-TAP™ programmable switch, you are able to select one of three different programs. To change to the next program, starting from the "Off" position, tap the switch rapidly 9 times (within 0.4 seconds per tap) and hold it down the 10th time. Continue holding the switch until the light turns off (approximately 1 second), and then release the switch. Repeat this pattern to change to the next program.

Available programs are High-Strobe-Low (Factory Default), High Only or Low-High.

