



NOTES:

1. ITEM: Needle Valve
2. REVERSE FREE FLOW: No
3. MAX. FLOW - HYDRAULIC VALVES: 15.0 gpm
4. BODY MATERIAL - HYDRAULIC VALVES: Brass
5. MAX. PRESSURE - HYDRAULIC VALVES: 2000 psi
6. INLET PORT SIZE - HYDRAULIC VALVES: 1/2" NPT
7. OUTLET PORT SIZE - HYDRAULIC VALVES: 1/2" NPT
8. VALVE TYPE - HYDRAULIC VALVES: Hydraulic Needle Valve

COMPONENT		Hydraulic Control Valves	
1A864		UNIT	
		INCH	
Needle Valve, Brass, 1/2-14, 15 GPM		SHEET	
		1 of 1	



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.84