



#### NOTES:

1. ITEM: Elbow, 90°
2. MAX. PRESSURE: 125 psi
3. TEMP. RANGE: -20° to 400°F
4. PIPE SIZE - PIPE FITTING: 2"
5. FITTING CONNECTION TYPE: FNPT
6. FITTING SCHEDULE/CLASS: Class 125
7. PIPE FITTING MATERIAL: Red Brass
8. STANDARDS: ASTM B584, ASME B16.15, ANSI B1.20.1

**GRAINGER**

100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
[www.grainger.com](http://www.grainger.com)

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

**SCALE** 0.65

COMPONENT		Brass Pipe Fitting	
1VEU4		UNIT	
		INCH	
		SHEET	
Elbow,90Deg Red Brass,2 In,150 PSI		1 of 1	