



NOTES:

1. ITEM: Street Elbow, 90°
2. MAX. PRESSURE: 125 psi
3. TEMP. RANGE: -20° to 400°F
4. PIPE SIZE - PIPE FITTING: 1/2"
5. PIPE FITTING MATERIAL: Red Brass
6. FITTING SCHEDULE/CLASS: Class 125
7. FITTING CONNECTION TYPE: MNPT x FNPT
8. STANDARDS: ASTM B584, ASME B16.15, ANSI B1.20.1

COMPONENT

Brass Pipe Fitting

UNIT

INCH

SHEET

1 of 1

GRAINGER
 // // // //

100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE

1.61

1VEW2

Street Elbow,90Deg Red Brass,1/2 In