



**NOTES:**

1. TUBE SIZE : 7/8
2. MAX. PRESSURE : 120 psi
3. TEMP. RANGE : -65° to 250°F
4. STANDARDS : NSF 61 ANNEX G
5. BASIC FITTING SHAPE : Union
6. TUBE FITTING MATERIAL : Low Lead Brass
7. FITTING CONNECTION TYPE: Compression



100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
[www.grainger.com](http://www.grainger.com)

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

**SCALE**

1.00

COMPONENT		Reducing Elbow	
20XM32		UNIT	
		INCH	
		SHEET	
Union Elbow, Low Lead Brass, 120 psi		1 of 1	