



#### NOTES:

1. CASTER STEM TYPE : Friction Ring
2. NUMBER OF WHEELS : 1
3. CASTER WHEEL/TREAD MATERIAL : Rubber
4. CASTER CORE MATERIAL : Rubber
5. FRAME FINISH : High Nickel
6. CASTER WHEEL BEARINGS : Plain
7. CASTER LOAD RATING RANGE : Light-Duty
8. LOAD RATING : 75 lb.
9. CASTER PRODUCT GROUP : Swivel Caster
10. APPLICATION : All Purpose Industrial and Commercial Casters

**GRAINGER**

100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
[www.grainger.com](http://www.grainger.com)

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

**SCALE**

0.72

**COMPONENT**

Stem Caster

**429H11**

Stem Caster, 2-1/2" Wheel Dia., 75 lb.

**UNIT**

INCH

**SHEET**

1 of 1