



NOTES:

- 1. HEAD TYPE : Hex
- 2. MATERIAL : Nylon
- 3. FINISH : Plain
- 4. THREAD STYLE : Fully Threaded
- 5. ROCKWELL HARDNESS : M61
- 6. SCREW INDUSTRY STANDARDS : ANSI/ASME B1.1 1982
- 7. TENSILE STRENGTH : 200 psi
- 8. THREAD TYPE : UNC (Coarse)

COMPONENT	Hex Head Cap Screw		
4AGV9	UNIT	INCH	
	SHEET	1 of 1	
	HHCS, 1/4-20x1, Nylon, Non Grd, Plain, PK10		
	SCALE	3.15	



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.