

**NOTES:**

1. ITEM: Street Elbow, 90°
2. TEMP. RANGE: -20° to 366°F
3. PIPE SIZE - PIPE FITTING: 1"
4. MAX. PRESSURE: 300 psi@150°F
5. FITTING SCHEDULE/CLASS: Class 150
6. PIPE FITTING MATERIAL: Malleable Iron
7. FITTING CONNECTION TYPE: MNPT x FNPT
8. STANDARDS: ASTM A-197, ASTM A47, ASME B16.3 and B16.4, UL Listed, FM Approved

**GRAINGER**  
/ / / /

100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 1.10

COMPONENT	Black Pipe Fitting	5P462
UNIT	INCH	
SHEET	Street Elbow, 90 Deg, 1 In., MNPT x FNPT	
1 of 1		