






NOTES:

- ITEM: Street Elbow, 90°
- PIPE SIZE - PIPE FITTING: 1-1/4"
- MAX. PRESSURE: 300 psi @ 150°F WOG
- FITTING SCHEDULE/CLASS: Class 150
- FITTING CONNECTION TYPE: FNPT x MNPT
- PIPE FITTING MATERIAL: Galvanized Malleable Iron
- STANDARDS: ASTM A-197, ASTM A47, ASME B16.3 and B16.4,
UL Listed, FM Approved, NSF-61 and AB1953 Listed

COMPONENT		Galvanized Pipe Fitting	
5P825 Street Elbow,90 Deg,1 1/4 In,Galvanized		UNIT	INCH
		SHEET	1 of 1

GRAINGER

100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.95